



PANDUIT P/N	WEIGHT
UICFP4**	.52 LB/10 PCS (236.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- FACEPLATE
 - 1- CLEAR SCREW COVER
 - 1- COLOR COORDINATED SCREW COVER
 - 2- CLEAR LABEL COVER
 - 2- MOUNTING SCREW



MODEL FILENAME		MO1279BB_UICFP4_03.PRT		SIZE A
DRAWING FILENAME		MO1279BB_DC_03A.PRT		
MINI-COM™ ULTIMATE ID™ 4 POSITION VERTICAL CLASSIC SERIES FACEPLATE CUSTOMER DRAWING				
  TM CORP. TINLEY PARK, ILL 60477		I.I. NUMBER N/A		
		PRODUCT SPEC N/A		
 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ±.03(.8) ANGLES ±		
DRAWN BY JsP		REVIEW DRAWING NUMBERS		
DATE 7-24-02		MATERIAL: ABS		
CHK'D		PART NO. UICFP4**		
		DRAWING NO. 01279-07		

R	7-24-02	JsP		RELEASED TO PRODUCTION	01279-07				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	