





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CMDB**-X	.10 LB/10 PCS (44.2 g/10 PCS)

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
  2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
  3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
  4. PART SNAPS INTO ALL MINI-COM TWO POSITION MODULE SPACES.



CAD FILENAME/LAYERS		M01019BD_DC_01A.PRT	
<h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS			
MINI-COM SVGA BLANK DUPLEX MODULE (CMDB**-X) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .03 (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY	JSP	MAT'L:	SCALE
DATE	1-26-01		NONE
CHECKED BY			DRAWING NO.
			01019-02
			DWG SIZE
			A

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
R	1-26-01	JSP		RELEASED TO PRODUCTION.	01019-02			