




SPECIFICATIONS:

PANDUIT TOOL NO: TGJT
TOOL WEIGHT (WITH LANYARD): 8.30 oz (235.3 gr.)

CUTS AND ASSEMBLES ALL TG STYLE COPPER JACK MODULES

THIS TOOL'S FEATURES INCLUDE:

- * SINGLE HANDLE TRIGGER FOR FAST INSTALLATION.
- * DUAL SIDE ACTION - ONE SIDE FOR CUTTING EXCESS WIRES AT WIRE CAP.
- ONE SIDE FOR ASSEMBLING CAP INTO JACKMODULE.
- * CUT-OFF CAPABILITY WITH THE COMPLETE HAND CYCLE.
- * TRIMMED WIRES HELD FOR EASY REMOVAL.
- * TOOL SPRING RETURNED TO OPEN POSITION.

DIMENSIONS SHOWN IN PARENTHESES ARE (mm) METRIC
(WITHOUT LANYARD): [DIMENSIONS ARE ROUNDED
AND SUBJECT TO CHANGE WITHOUT NOTICE.]

A = 5.75	(146.05)	OVERALL WIDTH
B = 5.11	(129.87)	OVERALL HEIGHT
C = 1.58	(40.23)	OVERALL DEPTH
D = 4.10	(104.04)	TOTAL HANDLE SPAN
E = 4.87	(123.60)	REAR HANDLE HEIGHT
F = 1.36	(34.54)	HEAD HEIGHT
G = 1.08	(27.31)	HEAD DEPTH
H = 0.74	(18.87)	HANDLE WIDTH
I = 0.21	(5.39)	OPENED BLADE GAP

TOOL DIV.
ENGINEERING DEPT.

DEC 29 2006

COPY

CAD FILENAME/LAYERS										R25199BA_DS_CP25199B01_00A									
PANDUIT										CORP TINLEY PARK, ILLINOIS									
CD * TGJT TOOL																			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±--- (.XX) ±---										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION									
DRAWN BY BJPU										MAT'L:									
DATE 8-23-06										SCALE 1/2" = 1"									
DRAWING NO. CP25199B01										DDB B									
REV										DATE									
BY										CHK									
DESCRIPTION										ECN - R CUST SUP									
00 12/28/06 BJPU RELEASED										4222 --									