


COVER REMOVED FOR CLARITY




MOUNTING HOLES -
FOR #6 PAN HEAD
SCREW (2 PLACES)



- 1.95
[49.5]


BREAKOUT AREA
(3 PLACES)





PANDUIT P/N	WEIGHT
CBX2**-AY	.62 LB/10 PCS (286.1 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. ALSO INCLUDED WITH BOX:
 - 1- BOX BASE
 - 1- BOX COVER
 - 1- PLT1.51-C PAN-TY
 - 2- MOUNTING SCREW
 - 1- STRIP OF 3.00" X .75" FOAM TAPE FOR MOUNTING
 - 1- ID LABEL KIT
5. BREAKOUTS DESIGNED TO ACCEPT LD3/LDP3 OR LD5/LDP5 RACEWAY.
6. BASE MATERIAL THICKNESS= .090(2.29)



NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

		SIZE A	
DRAWING FILENAME M02479EN_DC120_00A.PRT			
MINI-COM 2 POSITION SURFACE MOUNT BOX CUSTOMER DRAWING			
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477		I.I. NUMBER N/A	
		PRODUCT SPEC N/A	
 THIRD ANGLE PROJECTION		WORK INSTRUCTION N/A	
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± .031(.8) (.XXX) ± .010(.3) (.XX) ± .031(.8) ANGLES ±		SCALE NONE	
DRAWN BY JsP		PART NO. CBX2**-AY	
DATE 1-26-07		DRAWING NO. 02479-120	
CHK'D			
MATERIAL: ABS			