




NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. CONSTRUCTED WITH CAT6, 26AWG, STRANDED FULLY SHIELDED TWISTED PAIR, LSZH/CM CABLE.
3. DIMENSIONS IN PARENTHESES ARE IN FEET.
4. CABLE JACKET COLOR IS GRAY.
5. MATERIAL:

PLUG BOOT: PTE
PLUG: POLYCARBONATE
PLUG SHIELD: CARTRIDGE BRASS
JACK HOUSING: ABS
JACK SHIELD: PHOS BRONZE
CABLE JACKET: THERMOPLASTIC

EIA/TIA T568B WIRING SCHEME

PLUG POSITION	CABLE WIRE
1	RED
2	ORANGE
3	BLACK
4	BLUE
5	WHITE
6	GREEN
7	YELLOW
8	BROWN

FOR PART NUMBERS, SEE SHEET 2

1	8-30-07	BJN	EJH	A. FOR P/N F6JB5Z1B**MBLY ADDED LG: 4M, 6M, 9M, 11-14M, 16M, 18M, 22-28M, AND 32-50M	02479-310		REGA		
R	3-18-06	LZ	CEF	RELEASED TO PRODUCTION	02479-310	CEF	CEF		CEF
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP

MODEL FILENAME		SIZE
DRAWING FILENAME		A
M02479LW_DC310_00B		
CAT6 SHIELDED JACK TO PLUG ZONE PATCH CORD CUSTOMER DRAWING		
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477		I.I. NUMBER
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.		PRODUCT SPEC/ PKG SPEC
DIMENSIONAL TOLERANCES ARE: (.X) ±.06 (.XXX) ± (.XX) ± ANGLES ±		ASSY METHOD/ TEST METHOD
THIRD ANGLE PROJECTION		SCALE
DRAWN BY: LZ		NONE
DATE: 3-18-06		PART NO.
CHK'D: CEF		F6JBP5Z1B**MBLY
		DRAWING NO.
		02479-310
		SHEET 1 OF 2

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	MINIMUM CABLE LENGTH
F6JBP5Z1B3MBLY	3 M (9.8 FT)
F6JBP5Z1B4MBLY	4 M (13.1 FT)
F6JBP5Z1B5MBLY	5 M (16.4 FT)
F6JBP5Z1B6MBLY	6 M (19.7 FT)
F6JBP5Z1B7MBLY	7 M (23.0 FT)
F6JBP5Z1B8MBLY	8 M (26.2 FT)
F6JBP5Z1B9MBLY	9 M (29.5 FT)
F6JBP5Z1B10MBLY	10 M (32.8 FT)
F6JBP5Z1B11MBLY	11 M (36.1 FT)
F6JBP5Z1B12MBLY	12 M (39.4 FT)
F6JBP5Z1B13MBLY	13 M (42.7 FT)
F6JBP5Z1B14MBLY	14 M (45.9 FT)
F6JBP5Z1B15MBLY	15 M (49.2 FT)
F6JBP5Z1B16MBLY	16 M (52.5 FT)
F6JBP5Z1B18MBLY	18 M (59.1 FT)
F6JBP5Z1B20MBLY	20 M (65.6 FT)
F6JBP5Z1B22MBLY	22 M (72.2 FT)
F6JBP5Z1B24MBLY	24 M (78.7 FT)
F6JBP5Z1B26MBLY	26 M (85.3 FT)
F6JBP5Z1B28MBLY	28 M (91.9 FT)
F6JBP5Z1B30MBLY	30 M (98.4 FT)
F6JBP5Z1B32MBLY	32 M (105.0 FT)
F6JBP5Z1B34MBLY	34 M (111.5 FT)
F6JBP5Z1B36MBLY	36 M (118.1 FT)
F6JBP5Z1B38MBLY	38 M (124.7 FT)
F6JBP5Z1B40MBLY	40 M (131.2 FT)
F6JBP5Z1B42MBLY	42 M (137.8 FT)
F6JBP5Z1B44MBLY	44 M (144.4 FT)
F6JBP5Z1B46MBLY	46 M (150.9 FT)
F6JBP5Z1B48MBLY	48 M (157.5 FT)
F6JBP5Z1B50MBLY	50 M (164.0 FT)



MODEL FILENAME		SIZE A
DRAWING FILENAME M02479LW_DC310_00B		
CAT6 SHIELDED JACK TO PLUG ZONE PATCH CORD CUSTOMER DRAWING		
PANDUIT ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	
	PRODUCT SPEC/ PKG SPEC	
 THIRD ANGLE PROJECTION	ASSY METHOD/ TEST METHOD	
	SCALE NONE	
DRAWN BY LZ	REVIEW DRAWING NUMBERS	
DATE 3-18-06	PART NO. F6JBP5Z1B***MBLY	
CHK'D CEF	DRAWING NO. 02479-310 SHEET 2 OF 2	

I	8-28-07	BJN	EJH	FOR REVISIONS, SEE SHEET 1	02479-310		REGA			
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH