



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- NOTES:
- \*\*1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
  2. TWO (2) #6-32 X 1/4" SLOTTED OVAL HEAD SCREWS ARE INCLUDED WITH THIS PART.
  3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
  4. PART ACCEPTS 3 TYPES OF GFCI MODULE FRAMES, CFG1, CFG2, AND CFG4.



PANDUIT P/N	WEIGHT
CPG**	.34 LB/10 PCS (152.9/10 PCS)

CAD FILENAME/LAYERS MO0122BA\_DC\_00A.PRT

PANDUIT		CORP. TINLEY PARK, ILLINOIS	
DESIGNER SERIES "GFCI"		FACEPLATE (CPG**)	
CUSTOMER DRAWING		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.010(.3) (.XX) ±.031(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RCA	MAT'L: ABS	SCALE NONE	DWG NO. 00122-02
DATE 08-22-97	CHECKED BY	SIZE A	
REV	DATE	BY	CHK
R	08-22-97	RCA	RELEASED TO PRODUCTION.
			DESCRIPTION
	ECN	CHK	CUST
	00122-02		SUP