



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UICMPPK6G24BL	.88 LB/EACH PC (401.1 G/EACH PC)



- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 - DIMENSIONS IN PARENTHESES ARE IN METRIC.
 - PART INCLUDES:
 - 1- INSTRUCTION SHEET
 - 1- METAL STAMPING
 - 6- 4 POSITION FACEPLATE WITH 1 ULTIMATE ID LABEL POCKET (ASSEMBLED TO METAL STAMPING)
 - 1- TERMINATION TOOL
 - 6- CLEAR LABEL COVER
 - 1- #12-24 SCREW KIT (INCLUDES FOUR SCREWS)
 - 1- M6 SCREW KIT (INCLUDES FOUR SCREWS)
 - 24- MINI-COM TX6 PLUS JACK MODULE
 - LABELS SOLD SEPARATELY.
 - PATCH PANELS ACCEPT SNAP-IN MINI-COM MODULES.
 - DIMENSIONS IN () ARE IN METRIC.



MODEL FILENAME	SIZE
MO1207AB_UICMP24BL_07.PRT	A
DRAWING FILENAME	
MO0741NO_DC135_00A.PRT	

MINI-COM ULTIMATE ID 24 PORT
TX6 PLUS MODULAR PATCH PANEL KIT
CUSTOMER DRAWING

1:1. NUMBER	N/A
PRODUCT SPEC	N/A
WORK INSTRUCTION	N/A
SCALE	NONE
PART NO.	UICMPPK6G24BL
DRAWING NO.	00741-135

ALL DIMENSIONS ARE GIVEN IN INCHES. DIMENSIONAL TOLERANCES ARE: (.XX) ± .001(.01) ANGLES ± .010(.31)	
THIRD ANGLE PROJECTION	
DRAWN BY	JSP
DATE	10-5-06
PREVIEW DRAWING IMAGES	

STAMPING: C.R.S. FACEPLATES: ABS	
REVIEW DRAWING IMAGES	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	10-5-06	JSP	MJD	RELEASED TO PRODUCTION	00741-135				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH