






PAN-TY LOOPS FOR  
CABLE HOLD-DOWNS  
(4 PLACES)

POST FOR TAMPER  
RESISTANT SCREW



PANDUIT P/N	WEIGHT
CBX12**-AY	2.87 LB/10 PCS (1306 g/10 PCS)

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [ ] ARE IN METRIC.
4. BOX INCLUDES:
  - 1- BOX BASE
  - 1- BOX COVER
  - 4- PLT1.51-M PAN-TY
  - 1- LABEL/ LABEL COVER
  - 2- MOUNTING SCREW
  - 1- MOUNTING SCREW (USED TO SECURE COVER TO BASE)
  - 2- STRIP OF 3.00" X .75" FOAM TAPE FOR MOUNTING
5. BASE HAS FOUR POCKETS FOR OPTIONAL MAGNET (CBM-X)
6. BREAKOUTS DESIGNED TO ACCEPT LD5/LDP5 AND LD5/LDP10 RACEWAY.
7. BASE MATERIAL THICKNESS= .090[ 2.29 ].

DRAWING FILENAME		SIZE
MO2479EX_DC130_00A.PRT		A
MINI-COM 12 POSITION SURFACE MOUNT BOX CUSTOMER DRAWING		
 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477		1.1. NUMBER N/A
		PRODUCT SPEC N/A
 THIRD ANGLE PROJECTION		WORK INSTRUCTION N/A
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.  DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .0101(.3) (.XX) ± .031(.8) ANGLES ±		SCALE NONE
DRAWN BY JsP		PART NO. CBX12***-AY
DATE 12-27-06		BOX: ABS
CHK'D 		DRAWING NO. 02479-130