

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

GRIP SPAN:

1.5" (38.1 mm)
FULLY CLOSED

6.5" (165.0 mm)
FULLY OPEN

FULL STROKE COMPELLING DEVICE

MANUAL RACHET

"P" CODE DIE DETAIL

REPLACEABLE DIE SET
SEE SHEET 2



.260" (6.6 mm)

FULLY CLOSED HANDLE GAP

2.96" (75.3) mm

1.60" (40.6 mm)

8.66 " (220.0 mm)

SEE SHEET 2 FOR SPECIFICATIONS

PANDUIT CORP. TINLEY PARK, ILLINOIS

FCRP5 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
1.X1 ± 1.XXX1 ±
(.XX1) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DESIGNED BY DS/JW

MATERIAL:

SCALE

NONE

DATE 9.05.01

SHEET 1 OF 2

DRAWING NO.

TP24600A01

DWG

A

SIZE

00 9.05.01 JPW RLO

RELEASED*RPLCS TD23993C01

3985

RFL

REV DATE BY CHK

DESCRIPTION

ECN - R

CUST

SUP

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES UNLESS OTHERWISE SPECIFIED:

PANDUIT TOOL NUMBER **FCRP5** FIBER OPTIC HAND TOOL CRIMPS .048, .100, .128, .151, AND .190 HEX SIZES.

TOOL FEATURES:

CUSHION HAND GRIPS

CONTROLLED CYCLE

REPLACEABLE DIE SET PART NUMBER = **CD-FCRP5**

TOOL WEIGHT = 1.20 LBS / 30.5 Kg

ADDITIONAL DIMENSIONS:

.96" (24.4 mm) MAXIMUM HANDLE WIDTH

.93" (23.5 mm) MAXIMUM TOOL NOSE WIDTH

SEE SHEET 1 FOR TOOL DIMENSIONS

PANDUIT CORP. TINLEY PARK, ILLINOIS

FCRP5 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
1.X) ± 1.XXX) ±
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY **DS/JW**

MAT'L 1

SCALE **NONE**

DATE **9.05.01**

SHEET 2 OF 2

DRAWING NO.

TP24600A01

DWG
SIZE
A

00 9.05.01 SEE SHEET 1 FOR RELATED INFO

3985

.....

RFL

.....

CHK'D
RLO

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
-----	------	----	-----	-------------	-----	---	------	-----