


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:


1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PIGTAIL LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	06-04-07	MC		RELEASED TO PRODUCTION	02779-31				

900µm BUFFERED FIBER OPTIC SC PIGTAIL  
CUSTOMER DRAWING



**PANDUIT**™  
CORP.  
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES,  
UNLESS OTHERWISE SPECIFIED.  
DIMENSIONAL TOLERANCES ARE:  
(.X) (.XXX)  
(.XX) ANGLES

DRAWING FILENAME  
M02779CA\_DC\_00A.prt

SCALE  
NONE

DRAWN BY  
MC

MAT'L:

PART NO.  
SEE TABLE, SHT. 2

DATE  
05-22-07

DRAWING NO.  
02779-31  
(SHT. 1 of 2)

SIZE  
A



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

900um BUFFERED FIBER OPTIC SC PIGTAIL							
PANDUIT PART NO.	BUFFERED FIBER				SC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR
FXB3-NM*Y	NO FLAME RATING	10GbE 50/125um OM3	SIMPLEX 900um BUFFERED FIBER	BLUE	0.30dB	26dB	ELECTRIC IVORY
F5B3-NM*Y		50/125um OM2		BLUE	0.30dB	20dB	ELECTRIC IVORY
F6B3-NM*Y		62.5/125um OM1		BLUE	0.30dB	20dB	ELECTRIC IVORY
F9B3-NM*Y		9/125um OS1		BLUE	0.75dB	55dB	BLUE

\* - DENOTES PIGTAIL LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	06-04-07	MC		RELEASED TO PRODUCTION	02779-31				

900um BUFFERED FIBER OPTIC SC PIGTAIL CUSTOMER DRAWING									
				<b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477					
 THIRD ANGLE PROJECTION				ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03   (.XXX) ±.010   (.3) ±.005 (.XX) ±.03   (.8) ANGLE				DRAWING FILENAME M02779CA_DC_00A.prt	
				DRAWN BY MC				SCALE NONE	
				DATE 05-22-07				PART NO. SEE TABLE	
				CHK'D				DRAWING NO. 02779-31 (SHT. 2 of 2)	
								SIZE A	