



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.*	DESCRIPTION	WEIGHT
DP245E88TV25	24 PORT 4 PAIR CAT5E RJ21 PATCH PANEL	1.0 lb (466g)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM AS WELL AS OPTIONAL SNAP-IN LABEL HOLDERS.
- 24 PORT PATCH PANEL ALL PAIR WIRED 8 POSITION RJ45 MODULE ALL POSITIONS WIRED.
- THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) METRIC M6x1x15MM SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- MATERIALS- STAMPING: CRS
MODULE: V-O ABS

MODEL FILENAME	M02829AC_4PAIR_5E_24PORT_00	SIZE	A
DRAWING FILENAME	M02829AC_DC13_00C.PRT		
TITLE	24 PORT 4 PAIR CAT 5e RJ21 PATCH PANEL CUSTOMER DRAWING		
		I.I. NUMBER	
		PRODUCT SPEC	
	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°	WORK INSTRUCTION	
		SCALE NONE	
DRAWN BY	NER	REVIEW DRAWING NUMBERS	
DATE	8-17-07	PART NO.	
CHK'D	MKY	DRAWING NO.	
		02829-13 SHEET 1 OF 2	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
2	12-13-07	MDJr	MKY	C. ADDED 2 MISSING DIMENSIONS.	02829-13	MKY			MKY
1	10-31-07	MDJr	MKY	B. ADDED (4 PLACES). A. LABEL PART# WAS DPLT.	02829-13	MKY	RDE		MKY
R	8-17-07	NER	CEF	RELEASED TO PRODUCTION	02829-13	CEF	CEF		CEF

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

WIRING CHART (PORTS 1-3)			
RJ21 POSITIONS	RJ45 PLUG POSITION	PAIRS	PORT
26	5	PAIR 1	PORT 1
1	4		
27	1	PAIR 2	
2	2		
28	3	PAIR 3	
3	6		
29	7	PAIR 4	
4	8		
30	5	PAIR 5	PORT 2
5	4		
31	1	PAIR 6	
6	2		
32	3	PAIR 7	
7	6		
33	7	PAIR 8	
8	8		
34	5	PAIR 9	PORT 3
9	4		
35	1	PAIR 10	
10	2		
36	3	PAIR 11	
11	6		
37	7	PAIR 12	
12	8		

WIRING CHART (PORTS 4-6)			
RJ21 POSITIONS	RJ45 PLUG POSITION	PAIRS	PORT
38	5	PAIR 13	PORT 4
13	4		
39	1	PAIR 14	
14	2		
40	3	PAIR 15	
15	6		
41	7	PAIR 16	
16	8		
42	5	PAIR 17	PORT 5
17	4		
43	1	PAIR 18	
18	2		
44	3	PAIR 19	
19	6		
45	7	PAIR 20	
20	8		
46	5	PAIR 21	PORT 6
21	4		
47	1	PAIR 22	
22	2		
48	3	PAIR 23	
23	6		
49	7	PAIR 24	
24	8		
50	NONE	PAIR 25	
25			

2	12-13-07	MDJr	MKY	SEE SHEET 1 FOR REVISIONS	02829-13	MKY			MKY
1	10-31-07	MDJr	MKY	SEE SHEET 1 FOR REVISIONS	02829-13	MKY	RDE		MKY
R	8-17-07	NER	CEF	SEE SHEET 1 FOR REVISIONS	02829-13	CEF	CEF		CEF
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH

MODEL FILENAME		SIZE A
DRAWING FILENAME M02829AC_DC13_00C.PRT		
24 PORT 4 PAIR CAT 5e RJ21 PATCH PANEL CUSTOMER DRAWING		
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	
	PRODUCT SPEC/ PKG SPEC	
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°	
	ASSY METHOD/ TEST METHOD	
DRAWN BY NER	REVIEW DRAWING NUMBERS	
DATE 8-17-07	PART NO. SEE SHEET 1	
CHK'D MKY	DRAWING NO. 02829-13 SHEET 2 OF 2	