


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




| PANDUIT P/N | WEIGHT (APPROX.)   |
|-------------|--------------------|
| DPKR48688TG | 2.40 LB (1088.6 g) |

NOTES:


- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
- KIT INCLUDES THE FOLLOWING:
  - 1 - LABEL SET 1-24
  - 1 - LABEL SET 25-48
  - 1 - BLANK LABEL
  - 9 - LABEL HOLDERS
  - 1 - STRAIN RELIEF BAR
  - 1 - DP6 PLUS 48 PORT PATCH PANEL
  - 8 - 12-24 X 1/2" ROUND HEAD SCREWS
  - 4 - M6x1 X 15mm METRIC SCREWS
- MATERIAL:
  - PANEL HOUSING: STEEL
  - RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
  - PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
  - BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
  - RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
  - STRAIN RELIEF BAR: STEEL BAR STOCK
  - LABEL: VINYL
  - LABEL HOLDER: CLEAR VINYL
- 48 PORT PATCH PANEL 8 POSITION 8 WIRE.
- THE PATCH PANEL AND STRAIN RELIEF BAR ARE DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
- RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

FIGURE 1  
DP6 PLUS 48 PORT PATCH PANEL


|                                                                                                                                           |                          |                                         |
|-------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|-----------------------------------------|
| DRAWING FILENAME<br>M01537E0_DC54_00A.PRT                                                                                                 |                          | SIZE<br>A                               |
| DP6 PLUS 48 PORT PATCH PANEL<br>WITH STRAIN RELIEF BAR AND LABEL KIT<br>CUSTOMER DRAWING                                                  |                          |                                         |
|  <b>PANDUIT</b> ™<br>CORP.<br>TINLEY PARK, ILL 60477 | I.I. NUMBER              |                                         |
|                                                                                                                                           | PRODUCT SPEC/ PKG SPEC   |                                         |
| <br>THIRD ANGLE<br>PROJECTION                        | ASSY METHOD/ TEST METHOD |                                         |
|                                                                                                                                           | SCALE<br>NONE            |                                         |
| DRAWN BY<br>BJN                                                                                                                           | REVIEW DRAWING NUMBERS   | PART NO.<br>SEE CHART                   |
| DATE<br>11/26/07                                                                                                                          | MAT'L                    | DRAWING NO.<br>01537-54<br>SHEET 1 OF 2 |
| CHK'D<br>RJDU                                                                                                                             |                          |                                         |

| REV | DATE     | BY  | CHK  | DESCRIPTION           | ECN      | R | CUST | SUP | OTH |
|-----|----------|-----|------|-----------------------|----------|---|------|-----|-----|
| R   | 11/26/07 | BJN | RJDU | RELEASE TO PRODUCTION | 01537-54 |   | VMB  |     |     |


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




LABEL SET 1 - 24



LABEL SET 25 - 48



BLANK LABEL



LABEL HOLDER

FIGURE 2  
LABEL KIT




FIGURE 3  
STRAIN RELIEF BAR

|                                                                                          |                          |                          |
|------------------------------------------------------------------------------------------|--------------------------|--------------------------|
| MODEL FILENAME                                                                           |                          | SIZE                     |
| DRAWING FILENAME                                                                         |                          | A                        |
| M01537E0_DC54_00A.PRT                                                                    |                          |                          |
| DP6 PLUS 48 PORT PATCH PANEL<br>WITH STRAIN RELIEF BAR AND LABEL KIT<br>CUSTOMER DRAWING |                          |                          |
|                                                                                          | I.I. NUMBER              |                          |
|                                                                                          | PRODUCT SPEC/ PKG SPEC   |                          |
|                                                                                          | ASSY METHOD/ TEST METHOD |                          |
|                                                                                          | SCALE                    |                          |
| DRAWN BY                                                                                 | REVIEW DRAWING NUMBERS   | PART NO.                 |
| DATE                                                                                     |                          | SEE CHART                |
| CHK'D                                                                                    | MAT'L                    | DRAWING NO.              |
|                                                                                          |                          | 01537-54<br>SHEET 2 OF 2 |

|     |          |     |      |                                |          |   |      |     |     |
|-----|----------|-----|------|--------------------------------|----------|---|------|-----|-----|
| R   | 11/26/07 | BJN | RJDU | SEE SHT.1 FOR REVISION HISTORY | 01537-54 |   | VMB  |     |     |
| REV | DATE     | BY  | CHK  | DESCRIPTION                    | ECN      | R | CUST | SUP | OTH |