





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DUST CAPS REMOVED FOR CLARITY

NOTES:


1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT AND PACKAGE QUANTITIES.
2. MATERIALS:
 - a. PLATE: C.R.S. POWDER COATED
 - b. ADAPTER: COMPOSITE
 - c. SPLIT SLEEVE: ZIRCONIA
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
4. DIMENSIONS IN BRACKETS ARE METRIC.



12 POSITION KEYED DUPLEX LC FIBER ADAPTER PANEL
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ±.03 | (.XXX) ±.010 | (.3) ANGLES

DRAWING FILENAME
M01945ZW_DC_00A.prt

SCALE
NONE

DRAWN BY
MC

REVIEW DRAWING NUMBERS

PART NO.
SEE TABLE, SHT. 2

DATE
10-12-07



DRAWING NO.
01945-95
(SHT. 1 of 2)

SIZE
A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	10-17-07	MC		RELEASED TO PRODUCTION	01945-95				

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	ADAPTER KEY CODE	ADAPTER COLOR	SPLIT SLEEVE TYPE	WEIGHT
FAP12WABLDLCZ	A	BLACK	ZIRCONIA	1.40 lb/10 pcs (636.2 g/10 pcs)
FAP12WBRDDLDCZ	B	RED	ZIRCONIA	1.40 lb/10 pcs (636.2 g/10 pcs)
FAP12WCGRDLDCZ	C	GREEN	ZIRCONIA	1.40 lb/10 pcs (636.2 g/10 pcs)
FAP12WDYLDCZ	D	YELLOW	ZIRCONIA	1.40 lb/10 pcs (636.2 g/10 pcs)
FAP12WEORDLCZ	E	ORANGE	ZIRCONIA	1.40 lb/10 pcs (636.2 g/10 pcs)
FAP12WFDBDLCZ	F	DARK BLUE	ZIRCONIA	1.40 lb/10 pcs (636.2 g/10 pcs)

										12 POSITION KEYED DUPLEX LC FIBER ADAPTER PANEL CUSTOMER DRAWING	
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	
									 THIRD ANGLE PROJECTION	<small>ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.</small> <small>DIMENSIONAL TOLERANCES ARE:</small> (.X) ±.01 (.XXX) ±.010 (.0.3) (.XX) ±.03 0.8 ANGLES	DRAWING FILENAME M01945ZW_DC_00A.prt
										SCALE NONE	
									DRAWN BY MC	REVIEW DRAWING NUMBERS	
									DATE 10-15-07	PART NO. SEE TABLE	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	DRAWING NO. 01945-95 (SHT. 2 of 2)	SIZE A
R	10-17-07	MC		RELEASED TO PRODUCTION	01945-95					CHK'D	