




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD/PIGTAIL LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



LC CONNECTOR WITH 900um BOOT



										FIBER OPTIC 900um BUFFERED LC PIGTAIL CUSTOMER DRAWING					
										 PANDUIT TM CORP. TINLEY PARK, ILL 60477					
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.010 ANGLES		DRAWING FILENAME M02779CZ_DC/01A			
										 THIRD ANGLE PROJECTION		SCALE NONE			
										DRAWN BY EFK		REVIEW DRAWING NUMBERS		PART NO. SEE SHEET 2	
										DATE 09-09-09		DRAWING NO. 02779-63		SIZE A	
										CHK'D		SHEET 1 OF 2			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH						
R	09-09-09	EFK		RELEASED TO PRODUCTION	02779-63										

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FIBER OPTIC 900 μ m BUFFERED LC PIGTAIL							
PANDUIT PART NO.	CABLE				CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5B10-NM*	RISER (OFNR)	50/125 μ m	SIMPLEX 900 μ m BUFFERED FIBER	BLUE	0.25dB	20dB	BLACK
F6B10-NM*		62.5/125 μ m					ELECTRIC IVORY
FXB10-NM*		10GbE OM3			0.25dB	26dB	AQUA
FXOB10-NM*		OPTIMIZED 10GbE OM3					
FZB10-NM*		10GbE OM4			0.25dB	26dB	AQUA
FZOB10-NM*		OPTIMIZED 10GbE OM4					
F9B10-NM*		9/125 μ m OS1			0.35dB	55dB	BLUE

* - DENOTES PIGTAIL LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	09-09-09	EFK		RELEASED TO PRODUCTION	02779-63				

FIBER OPTIC 900 μ m BUFFERED LC PIGTAIL CUSTOMER DRAWING									
				PANDUIT TM CORP. TINLEY PARK, ILL 60477					
				ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.008 ANGLES				DRAWING FILENAME M02779CZ_DC/01A	
DRAWN BY EFK				REVIEW DRAWING NUMBERS				SCALE NONE	
DATE 09-09-09				AS NOTED				PART NO. SEE TABLE	
CHK'D				DRAWING NO. 02779-63				SIZE A	
SHEET 2 OF 2									