




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT P/N	ADAPTER COLOR	SPLIT SLEEVE TYPE
FAP8WAQDLC	AQUA	PHOS BRONZE
FAP8WBLDLC	BLACK	
FAP8WEIDLC	ELECTRIC IVORY	
FAP8WAQDLCZ	AQUA	ZIRCONIA
FAP8WBUDLCZ	BLUE	

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:
 - PLATE: C.R.S. POWDER COATED
 - ADAPTER: COMPOSITE, SEE TABLE
 - SPLIT SLEEVE: SEE TABLE
- DIMENSIONS IN BRACKETS ARE METRIC.



								8 POSITION DUPLEX LC FIBER ADAPTER PANEL CUSTOMER DRAWING			
								 PANDUIT ™ CORP. TINLEY PARK, ILL 60477			
								 THIRD ANGLE PROJECTION			
								ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ANGLES			
								DRAWING FILENAME MO1945AD_DC_02A			
								SCALE NONE			
								PART NO. SEE TABLE			
								DRAWING NO. 01945-09			
								SIZE A			
03	01-31-11	MC		RELEASED TO PRODUCTION	01945-09			SEE NOTES			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST				