



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	ADAPTER COLOR	SPLIT SLEEVE TYPE
FAP12WE1DLC	ELECTRIC IVORY	PHOS BRONZE
FAP12WAQDLC	AQUA	
FAP12WBLDLC	BLACK	
FAP12WBUDLCZ	BLUE	ZIRCONIA
FAP12WAQDLCZ	AQUA	

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:
 - PLATE: C.R.S. POWDER COATED
 - ADAPTER: COMPOSITE, ELECTRIC IVORY, BLUE OR AQUA.
 - SPLIT SLEEVE: SEE TABLE.
- DIMENSIONS IN BRACKETS ARE METRIC.



											12 POSITION DUPLEX LC FIBER ADAPTER PANEL CUSTOMER DRAWING						
												 TINLEY PARK, ILL 60477					
											 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.			DRAWING FILENAME MO1945AE_DC/01A		
										DIMENSIONAL TOLERANCES ARE: (.X) (.XXX)±.010 (0.3) (.XX)±.03 (0.8) ANGLES			SCALE NONE				
										DRAWN BY MYW			REVIEW DRAWING NUMBERS				
										DATE 04-21-05			PART NO. SEE TABLE				
03	01-31-11	EFK		RELEASED TO PRODUCTION	01945-14						SEE NOTES			DRAWING NO. 01945-14		SIZE A	
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH	CHK'D	TMS					