

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
BT2LH	.188 (4.8)	2.00 (51)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	8.7 (221)	120 (534)	LIGHT HEAVY	.59 (267)
BT3LH	.188 (4.8)	3.00 (76)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	11.8 (300)	120 (534)	LIGHT HEAVY	.79 (358)
BT4LH	.188 (4.8)	4.00 (102)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	14.9 (378)	120 (534)	LIGHT HEAVY	.99 (449)
BT5LH	.188 (4.8)	5.00 (127)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	18.1 (460)	120 (534)	LIGHT HEAVY	1.19 (540)
BT6LH	.188 (4.8)	6.00 (152)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	21.2 (538)	120 (534)	LIGHT HEAVY	1.39 (631)
BT7LH	.188 (4.8)	7.00 (178)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	24.4 (620)	120 (534)	LIGHT HEAVY	1.59 (722)
BT8LH	.188 (4.8)	8.00 (203)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	27.5 (699)	120 (534)	LIGHT HEAVY	1.79 (813)
BT9LH	.188 (4.8)	9.00 (229)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	30.7 (780)	120 (534)	LIGHT HEAVY	1.99 (904)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty CABLE TIES
BT SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±.10(2.5) (.XXX) ±.020(.51)
(.XX) ±.02(.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
PMH

MAT'L:

SCALE
NONE

6 5/2/06 JABC

REMOVED CURVED TIP REFERENCE &
TIP STYLE COLUMN

BT-0037 6

DATE
6-24-93

NYLON 6.6

DRAWING NO.
BT-0037

DWG
A

REV DATE BY CHK

DESCRIPTION

ECN - R CUST SUP

CHK'D
JVL

SHT. 3 OF 3

SIZE