


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



* PANDUIT PART NUMBER	BUNDLE DIA.		A In (mm)	B In (mm)	C In (mm)	D In (mm)	E In (mm)	F In (mm)	G In (mm)	H In (mm)	J In (mm)	WRITE-ON AREA in. (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./ 100 pcs. (g)
	MIN. In (mm)	MAX. In (mm)													
BF1M	.06 (1.5)	0.90 (23)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	4.6 (117)	.829 (21.1)	.381 (9.7)	.03 (.76)	.36 x .81 (9.1 x 20.6)	18 (80)	MINIATURE	.09 (42)
BF2M	.06 (1.5)	2.0 (51)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	8.3 (211)	.829 (21.1)	.381 (9.7)	.03 (.76)		18 (80)	MINIATURE	.16 (71)

NOTES:

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty CABLE TIES
BF SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .005 (XXX) ± .020 (.51)
(.XX) ± .02 (.51) ANGLES ± .005

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
TJ

MAT'L:

SCALE
NONE

DATE
5/14/97

NYLON 6.6

DRAWING NO.

BT-0249

DWG
A
SIZE

6	4/19/05	ERW		METRIC CONVERSION CORRECTIONS	0249	6									
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP							