


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION **	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT1.5I-120	.06 (1.5)	1.38 (35)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	5.6 (142)	25 (111)	I	CURVED	.12 (55)
PLT2S-120	.06 (1.5)	1.88 (48)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	7.4 (188)	40 (178)	S	CURVED	.26 (118)
PLT4S-120	.06 (1.5)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	40 (178)	S	CURVED	.47 (213)
PLT4H-120	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	14.5 (368)	90 (400)	H	STRAIGHT	1.21 (549)
PLT7LH-120	.188 (4.8)	8.00 (203)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	24.7 (627)	90 (400)	LH	STRAIGHT	1.98 (899)
PLT8LH-120	.188 (4.8)	8.00 (203)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	27.6 (701)	90 (400)	LH	STRAIGHT	2.01 (913)

NOTES:

- \* 1) SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, AND PART COLOR.
- \*\* 2) CABLE TIE CROSS SECTION CODE: M=MINIATURE, I=INTERMEDIATE, S=STANDARD, LH=LIGHT HEAVY & H=HEAVY
- 3) MATERIAL IS WEATHER RESISTANT AND HAS A LOW WATER ABSORPTION PERCENTAGE.
- 4) MATERIAL IS RESISTANT TO MOST SALTS & CHEMICALS.
- 5) MATERIAL HAS A UL RELATIVE THERMAL INDEX RATING OF 194°F (90°C).
- 6) MATERIAL HAS LOW TEMPERATURE TOUGHNESS DOWN TO -40°F (-40°C) WITH A NOTCHED IZOD RATING OF 1.3 ft lbs/in @ ROOM TEMPERATURE.

DIMENSIONS IN PARENTHESIS ARE IN METRIC W10035ER/01

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-TY CABLE TIES  
PLT SERIES

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± (.XXX) ± .020 (.51)  
(.XX) ± .02(.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
CEW  
DATE  
12/20/84  
CHK'D  
HVP

MAT'L:  
NYLON 12  
(BLACK)

SCALE  
NONE  
DRAWING NO.  
SS-19103

DWG  
A  
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
---	---	---	---	REVISED NOTE 1	---	---	---	---
---	---	---	---	CORRECTED 'C' DIMENSION OF PLT2S	---	---	---	---
---	---	---	---	ADDED PLT7LH-120	---	---	---	---
---	---	---	---	CORRECTED 'C' DIMENSION OF PLT4H	---	---	---	---
7	5/16/11	JABO	PBC	CORRECTED 'C' AND 'D' DIMENSION OF PLT8LH.	SS-19103	7	PBC	