


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	COLOR	UL LISTED * RATE LOAD lbs. (N)	APPROXIMATE WEIGHT lbs/10 ROLLS (g) (100 PIECES)
	MIN. (mm)	MAX. (mm)							
HLSP1.5S-X0	.25 (6.4)	1.5 (38.1)	.100 (2.5)	6.00 (152)	.750 (19.1)	2.8 (71)	BLACK	50 (222)	.43 (194)
HLSP1.5S-X12	.25 (6.4)	1.5 (38.1)	.100 (2.5)	6.00 (152)	.750 (19.1)	2.8 (71)	MAROON	50 (222)	.43 (194)
HLSP3S-X0	.25 (6.4)	3.2 (81.3)	.100 (2.5)	12.00 (305)	.750 (19.1)	3.6 (91)	BLACK	50 (222)	.84 (380)
HLSP3S-X12	.25 (6.4)	3.2 (81.3)	.100 (2.5)	12.00 (305)	.750 (19.1)	3.6 (91)	MAROON	50 (222)	.84 (380)
HLSP5S-X0	.25 (6.4)	5.0 (127)	.100 (2.5)	18.00 (457)	.750 (19.1)	4.5 (114)	BLACK	50 (222)	1.24 (562)
HLSP5S-X12	.25 (6.4)	5.0 (127)	.100 (2.5)	18.00 (457)	.750 (19.1)	4.5 (114)	MAROON	50 (222)	1.24 (562)




ILLUSTRATION "A"

NOTES:

- 1) HLSP TIES AVAILABLE IN BLACK AND MAROON ONLY.
- * 2) MINIMUM 2" (50.8 mm) OVERLAP REQUIRED TO ACHIEVE UL LISTED RATED LOAD. (1.5 IN² OR 968 mm²)
- 3) SUITABLE FOR USE IN AIR HANDLING SPACES PER NEC SEC. 300-22 (C) AND (D).
- 4) ALL LENGTHS PACKED IN ROLL FORM. (SEE ILLUSTRATION "A")

DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS

W10001DM/05-SS-27183

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES
HLSP SERIES
FLAMMABILITY RATING: UL 94-V2

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .035
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
K. TROST

MAT'L:

SCALE NONE

DATE
12-29-98

POLYPROPYLENE HOOK/
NYLON KNIT LOOP

DRAWING NO.

SS-27183

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
5	2/3/10	JABO	TGS	CORRECTED -X0 UL LISTED RATE LOAD	SS-27183	5	TGS	

CHK'D
HVP