


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

DURA-TY CABLE TIES MEET OR EXCEED THE REQUIREMENTS OF TR-TSY-000789, TELCORDIA TECHNOLOGIES.

PANDUIT * PART NO.	DESCRIPTION	BUNDLE DIA.		A	B	C	D	E	F	MINIMUM LOOP TENSILE 2"/MIN. lbs. (N)	WEIGHT lbs/(kg) per 100/pcs
		MIN. in. (mm)	MAX. in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)		
DT4EH	13.5 IN. LONG TIE	.020 (.51)	3.875 (98.4)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	13.5 ± .150 (343) (±3.81)	250 (1112)	2.6 (1.18)
DT8EH	27 IN. LONG TIE	.020 (.51)	8.0 (203.2)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	27.0 ± .150 (686) (±3.81)	250 (1112)	4.4 (2.0)
DT14EH	48 IN. LONG TIE	.020 (.51)	14.0 (355)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	48.0 ± 1.50 (1219) (±38.1)	250 (1112)	7.5 (3.4)
DT15EH	53 IN. LONG TIE	.020 (.51)	15.0 (381)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	53.0 ± 1.50 (1346) (±38.1)	250 (1112)	8.1 (3.7)
DT28EH	96 IN. LONG TIE	.020 (.51)	28.0 (711)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	96.0 ± 1.50 (2438) (±38.1)	250 (1112)	13.8 (6.3)
DT44EH	144 IN. LONG TIE	.020 (.51)	44.0 (1117)	.059 (1.50)	.495 (12.57)	.490 (12.45)	.812 (20.62)	.718 (18.24)	144.0 ± 1.50 (3658) (±38.1)	250 (1112)	20.6 (9.3)

W10001BQ/04

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DURA-TY
EXTRUDED CABLE TIES (EXTRA HEAVY)

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	DRAWN BY	MAT'L;	SCALE	DWG
---	---			CHANGED WIDTH TOLERANCE FROM ±.008 TO ±.012.	---	---			JV		N/A	
4	11/10/08	ERW		CHANGED WIDTH (DIM 'B') ON ALL PARTS FROM .500 TO .495	SS-27250	4			DATE 3/16/00	STRAP & HEAD - BLACK ACETAL EACH HEAD HAS TWO, TYPE 302 STAINLESS STEEL BARBS	SS-27250	A
									CHK'D DWW		SHEET 1 OF 2	SIZE