


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs/100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
CBR1M	.070 (1.8)	1.0 (25.4)	.038 (1.0)	.098 (2.5)	.140 (3.6)	.208 (5.3)	.195 (5.0)	4.1 (104.1)	18 (80)	MINIATURE	.061 (27.7)
CBR1.5M	.070 (1.8)	1.5 (38.1)	.042 (1.1)	.098 (2.5)	.146 (3.7)	.208 (5.3)	.209 (5.3)	5.6 (142.2)	18 (80)	MINIATURE	.084 (38.3)
CBR2M	.070 (1.8)	2.0 (50.8)	.042 (1.1)	.098 (2.5)	.146 (3.7)	.208 (5.3)	.209 (5.3)	7.2 (182.9)	18 (80)	MINIATURE	.108 (48.8)
CBR1.5I	.070 (1.8)	1.5 (38.1)	.040 (1.0)	.140 (3.6)	.180 (4.6)	.250 (6.4)	.250 (6.4)	5.9 (149.9)	40 (178)	INTERMEDIATE	.129 (58.5)
CBR3I	.070 (1.8)	3.0 (76.2)	.052 (1.3)	.140 (3.6)	.192 (4.9)	.250 (6.4)	.262 (6.7)	10.4 (264.2)	40 (178)	INTERMEDIATE	.26 (119.3)
CBR4I	.070 (1.8)	4.0 (101.6)	.052 (1.3)	.140 (3.6)	.192 (4.9)	.250 (6.4)	.262 (6.7)	13.6 (345.4)	40 (178)	INTERMEDIATE	.34 (153.2)

NOTE(S):

- * SEE CURRENT PRICE SHEET TO DETERMINE PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

SS-27318-00

PANDUIT CORP. TINLEY PARK, ILLINOIS

CBR SERIES CABLE TIE

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±.01(.25) (.XXX) ±.020(.51)
(.XX) ±.02(.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
--	----	--		CORRECTED MATERIAL NAME	----	--		
3	5/31/06	JABO		CORRECTED CBR1M CROSS-SECTION TYPO	27318	3		

DRAWN BY
JABO
DATE
6/22/01
CHK'D
JRJR

MAT'L:
NYLON 6.6

SCALE
NONE
DRAWING NO.
SS-27318
DWG
A
SIZE