


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	DESCRIPTION	BUNDLE DIA.		A in (mm)	B ft (m)	C in (mm)	D in (mm)	E in (mm)	MIN. LOOP* TENSILE lbs.(N)	APPROXIMATE WEIGHT lbs/ROLL (g)
		MIN. in (mm)	MAX.							
TTS-20R0	20 FEET (6.1m) ROLL	.625 (16)	VARIOUS	.035 (0.9)	20 (6.1)	.750 (19.1)	1.5 (38)	3.25 (83)	40 (178)	.072 (33)
TTS-35RX0	35 FEET (10.7m) ROLL	.625 (16)	VARIOUS	.035 (0.9)	35 (10.7)	.750 (19.1)	1.5 (38)	4.0 (102)	40 (178)	.128 (58)
TTS-35R3-0										

NOTES:

- \* 1. MINIMUM 2" (50.8mm) OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.
- 2. COLOR: BLACK
- 3. A MAXIMUM OF ONE SPLICE PER ROLL IS ACCEPTABLE. SPLICE TO BE A 2" OVERLAP OF MATERIAL.

CAD FILE/LAYERS SS-27348/04  
DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS  
TAK-TAPE ROLLS  
TTS SERIES

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± (.XXX) ± .030  
(.XX) ± .125 ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

4	1/31/12	ARHA	DJW	ADDED NOTE 3.	SS-27348	4	KLN						
--	-----	---		CHANGED APPROX. WEIGHT COLUMN FROM "LBS/10 ROLLS" TO "LBS/ROLL"	-----	--							
3	3/30/07	ERW	DWW	ADDED TTS-35R3-0	27348	3	TGS						
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP					

DRAWN BY  
JABO  
DATE  
2/7/02  
CHK'D  
DWW

MAT'L:  
POLYPROPYLENE HOOKS/  
NYLON LOOPS

SCALE NONE  
DRAWING NO.  
SS-27348  
DWG  
A  
SIZE