

Technical drawing of a probe assembly, showing side and end views with dimensions and labels.

Labels:

- NYLON PLASTIC CINCH RING
- C REF.
- BRASS GROMMET & WASHER
- INSIDE DIAMETER: .250"-.265" (6.35-6.73mm)
- RECOMMENDED FASTENER: #12 SCREW OR M5 SCREW
- B
- F REF.
- A
- D

Dimensions:

- E
- G
- .155" MAX. (3.94 mm)

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PARTS (g)
	MIN. in (mm)	MAX. in (mm)										
UGCTC3S	1.0 (25.4)	3.0 (76.2)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	12.0 (305)	.88 (22.4)	50 (222)	STANDARD	.81 (368)
UGCTC5S	1.0 (25.4)	5.0 (127)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	18.0 (457)	.88 (22.4)	50 (222)	STANDARD	1.01 (456)

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

SS_27381_00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES
ULTRA-CINCH HOOK & LOOP TIES
CENTER MOUNT GROMMET

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .25 (.XXX) ± .030
(.XX) ± .125 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JABO	
------------------	--

MAT'L:

DATE	10/16/02
------	----------

WOVEN NYLON
HOOK/LOOP
COLOR: BLACK
EXCEPT GROMMET

SCALE	NONE
-------	------

DRAWING NO.

SS-27381

DWG
A
SIZE

7	4/12/06	FAB		ADDED WEIGHT TO DRAWING	27381	7			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	