

Technical drawing of a cable assembly showing side and end views with dimensions A through F and labels for components like Nylon Plastic Cinch Ring and Brass Grommet & Washer.

Labels:

- NYLON PLASTIC CINCH RING
- BRASS GROMMET & WASHER
- INSIDE DIAMETER: .250"-.265" (6.35-6.73mm)
- RECOMMENDED FASTENER: #12 SCREW OR M5 SCREW
- GROMMET THICKNESS
- .155" MAX. (3.94 mm)

Dimensions:

- A: Cable diameter
- B: Distance from cinch ring to end of cable
- C REF.: Distance from cinch ring to grommet
- D: Grommet thickness
- E: Distance from cinch ring to grommet
- F REF.: Total length of cable assembly
- G: Distance from cinch ring to grommet
- H: Distance from cinch ring to grommet

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PARTS (g)
	MIN. in (mm)	MAX. in (mm)											
UGCTE3S	1.0 (25.4)	3.0 (76.2)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	12.0 (305)	1.7 (43)	.6 (15)	50 (222)	STANDARD	.87 (396)
UGCTE5S	1.0 (25.4)	5.0 (127)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	18.7 (475)	1.7 (43)	.6 (15)	50 (222)	STANDARD	1.08 (490)

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

SS_27385.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES
ULTRA-CINCH HOOK & LOOP TIES
END MOUNT GROMMET

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ± .25	(.XXX) ± .030
(.XX) ± .125	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JABO

MAT'L:

SCALE NONE

DATE
10/22/02

WOVEN NYLON
HOOK/LOOP

COLOR: BLACK
EXCEPT GROMMET

DRAWING NO.

SS-27385

DWG
A
SIZE

6	4/12/06	FAB		ADDED WEIGHT TO DRAWING	27385	6			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	