


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT<br>PART NO. * | BUNDLE DIA.     |                 | A<br>in<br>(mm) | B<br>in<br>(mm) | C<br>in<br>(mm) | D<br>in<br>(mm) | E<br>in<br>(mm) | F<br>in<br>(mm) | MIN. LOOP<br>TENSILE lbs.<br>** (N) | CROSS<br>SECTION | TIP<br>STYLE | WEIGHT<br>lbs./100 pcs.<br>(g) |
|-----------------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-------------------------------------|------------------|--------------|--------------------------------|
|                       | MIN. in<br>(mm) | MAX. in<br>(mm) |                 |                 |                 |                 |                 |                 |                                     |                  |              |                                |
| PLT1M-71              | .06<br>(1.5)    | .87<br>(22)     | .048<br>(1.2)   | .101<br>(2.6)   | .192<br>(4.9)   | .130<br>(3.3)   | .190<br>(4.8)   | 4.00<br>(101.6) | 35 (156)                            | MINIATURE        | CURVED       | .08 (36)                       |
| PLT1.5M-71            | .06<br>(1.5)    | 1.38<br>(35)    | .048<br>(1.2)   | .101<br>(2.6)   | .192<br>(4.9)   | .130<br>(3.3)   | .190<br>(4.8)   | 5.90<br>(149.9) | 35 (156)                            | MINIATURE        | CURVED       | .11 (52)                       |
| PLT2S-71              | .13<br>(3.3)    | 1.88<br>(48)    | .055<br>(1.4)   | .190<br>(4.8)   | .260<br>(6.6)   | .240<br>(6.1)   | .320<br>(8.1)   | 7.40<br>(188)   | 150 (668)                           | STANDARD         | STRAIGHT     | .38 (173)                      |

NOTES:

- \*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2) MATERIAL HAS A UL RELATIVE THERMAL INDEX RATING OF 500°F (260°C).
- 3) MATERIAL FLAMMABILITY RATING: UL94V-0.
- 4) EXCELLENT RESISTANCE TO MOST CHEMICALS.
- \*\*5) MINIMUM LOOP TENSILE RATING AT 73°F (23°C).

WI0035DS/03 SS-27424.PRT

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

|     |          |     |     |                                               |  |  |       |   |      |      |                                                                                                                                   |                                   |                                                                                               |                         |          |
|-----|----------|-----|-----|-----------------------------------------------|--|--|-------|---|------|------|-----------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|-----------------------------------------------------------------------------------------------|-------------------------|----------|
|     |          |     |     |                                               |  |  |       |   |      |      | PANDUIT CORP. TINLEY PARK, ILLINOIS                                                                                               |                                   |                                                                                               |                         |          |
|     |          |     |     |                                               |  |  |       |   |      |      | PAN-TY CABLE TIES<br>PLT ELEVATED TEMPERATURE SERIES                                                                              |                                   |                                                                                               |                         |          |
|     |          |     |     |                                               |  |  |       |   |      |      | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ± .1(2.5)(.XXX) ± .020(.51)<br>(.XX) ± .02(.51) ANGLES ± ----- |                                   | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |                         |          |
|     |          |     |     |                                               |  |  |       |   |      |      | DRAWN BY<br>JABO                                                                                                                  | MAT'L: PEEK<br>COLOR: BROWN       |                                                                                               | SCALE<br>NONE           |          |
| 6   | 10/11/10 | BWG | MPH | UPDATED 1M AND 1.5M DIMENSIONS B, D, E AND F. |  |  | 27424 | 6 |      | BOBK | DATE<br>06/01/04                                                                                                                  | REG. T.M. OF<br>VICTREX MFG. LTD. |                                                                                               | DRAWING NO.<br>SS-27424 | DWG<br>A |
| REV | DATE     | BY  | CHK | DESCRIPTION                                   |  |  | ECN   | R | CUST | SUP  | CHK'D<br>DM                                                                                                                       |                                   |                                                                                               | SIZE                    |          |