



## INSTALLATION INSTRUCTIONS

Printed In USA

**SPEC  
GRADE**

## INSTALLATION INSTRUCTIONS

**NOTICE:** Connect only copper or copper-clad wire to this device.



**WARNING:** Turn off power to circuit before installing this device. Improper wiring of any electrical device can cause serious injury or death and should only be installed by an Electrician or other qualified person.

- **STRIP WIRES** – one inch for side wire looping. For back wiring, see strip gage on device.
- **CONNECT WIRES** to terminals per diagram on back panel. Terminals will accept #10 – #14 AWG. Select appropriate wire size in accordance with NEC and local codes. Do **NOT** tin stranded conductors.
- **INSTALL DEVICE** in wall box using mounting screws provided. Install cover plate (not provided).

- **CONNECT WIRES** to terminals per diagram on back panel. Terminals will accept #10 – #14 AWG. Select appropriate wire size in accordance with NEC and local codes. Do NOT tin stranded conductors.

- **INSTALL DEVICE** in wall box using mounting screws provided. Install cover plate (not provided).

Instruction Sheet RW275

REVERSE SIDE

NOTES:

1. PANDUIT PART NUMBER RW275.
2. MATERIAL TO BE 50# WHITE OFFSET.
3. COLOR OF INK TO BE BLACK.
4. FOLD THE 5-1/2" X 8-1/2" TO  
5-1/2" X 4-1/4" WITH THE WIRING  
DIAGRAM EXPOSED ON FRONT SIDE.  
THEN FOLD AGAIN TO 2-3/4" X 4-1/4"  
WITH "PRINTED IN USA" ON FRONT.
5. BAND IN 100 PER BUNDLE.

2. MATERIAL TO BE 50# WHITE OFFSET.

3. COLOR OF INK TO BE BLACK.

4. FOLD THE 5-1/2" X 8-1/2" TO 5-1/2" X 4-1/4" WITH THE WIRING DIAGRAM EXPOSED ON FRONT SIDE. THEN FOLD AGAIN TO 2-3/4" X 4-1/4" WITH "PRINTED IN USA" ON FRONT.
5. BAND IN 100 PER BUNDLE.

5. BAND IN 100 PER BUNDLE.

[illegible]

2

1