

Cable Accessories for Building and Construction

J-Pro™ System Description	Hook Size	B-Line	ERICO (CADDY*)	Panduit
---------------------------	-----------	--------	----------------	---------

Wall Mount

One 1/4" (M6) mounting hole for user supplied screw	3/4"	BCH12	CAT12	JP75W-L20
	1 5/16"	BCH21	CAT21	JP131W-L20
	2"	BCH32	CAT32	JP2W-L20
	4"	BCH64	CAT64	JP4W-X20

Wall Mount – Powder Actuated

One 5/32" (M4) and one 1/4" (M6) mounting hole for user supplied fasteners	3/4"	BCH12	CAT12	JP75WP2-L20
	1 5/16"	BCH21	CAT21	JP131WP2-L20
	2"	BCH32	CAT32	JP2WP2-L20
	4"	BCH64	CAT64	JP4WP2-X20

Ceiling Mount

One 3/16" (M5), 1/4" (M6), and 3/8" (M10) mounting hole	3/4"	BCH12-RB	CAT12AB	JP75CM-L20	
	1 5/16"	BCH21-RB	CAT21AB	JP131CM-L20	
	1 5/16"	BCH21-RB	CAT21AFAB3	JP2CM-L20	
	1 5/16"	BCH21-RB	CAT21AFAB4		
	1 5/16"	BCH21-RB	CAT21AFAB6		
	2"	BCH32-RB	CAT32AB		
	2"	BCH32-RB	CAT32AFAB3		
	2"	BCH32-RB	CAT32AFAB4		
	2"	BCH32-RB	CAT32AFAB6		
	4"	BCH64-RB	CAT64AB		JP4CM-X20
	4"	BCH64-RB	CAT64AFAB3		
	4"	BCH64-RB	CAT64AFAB4		
	4"	BCH64-RB	CAT64AFAB6		

Drop Wire and Threaded Rod Clip

For use with #12 wire and threaded rod up to 3/8" diameter	3/4"	BCH12-W2	CAT124Z34	JP75DW-L20
	3/4"	BCH12-W6	CAT126Z34	JP131DW-L20
	1 5/16"	BCH21-W2	CAT214Z34	
	1 5/16"	BCH21-W6	CAT216Z34	
	2"	BCH32-W2	CAT324Z34	JP2DW-L20
	2"	BCH32-W6	CAT326Z34	

Z-Purlin Clips

For use with angled flanges up to 1/4" thick	3/4"	BCH12-F4	CAT12AF14	JP75ZP-L20
	1 5/16"	BCH21-F4	CAT21AF14	JP131ZP-L20
	2"	BCH32-F4	CAT32AF14	JP2ZP-L20
	4"	BCH64-F4	CAT64AF14	JP4ZP-X20

C-Purlin Clips

For use with vertical flanges up to 1/4" thick	3/4"	BCH12-F3	CAT12VF14	JP75CP-L20
	1 5/16"	BCH21-F3	CAT21VF14	JP131CP-L20
	2"	BCH32-F3	CAT32VF14	JP2CP-L20
	4"	BCH64-F3	CAT64VF14	JP4CP-X20

Contact factory for additional color options.



J-Pro™ System Description	Hook Size	B-Line	ERICO (CADDY*)	Panduit
---------------------------	-----------	--------	----------------	---------

Screw-On Beam Clamp

For use with flanges up to 1/2" thick	3/4"	BCH12-C1	CAT12BC	JP75SBC50-L20
	1 5/16"	BCH21-C1	CAT21BC	JP131SBC50-L20
	2"	BCH32-C1	CAT32BC	JP2SBC50-L20
	4"	BCH64-C1	CAT64BC	JP4SBC50-X20
For use with flanges up to 3/4" thick	3/4"	BCH12-C442A	CAT12BC200	JP75SBC87-L20
	1 5/16"	BCH21-C442A	CAT21BC200	JP131SBC87-L20
	2"	BCH32-C442A	CAT32BC200	JP2SBC87-L20
	4"	BCH64-C442A	CAT64BC200	JP4SBC87-X20
For use with flanges up to 1/2" thick, rotates 360 degrees	3/4"	BCH12-C2	CAT12BCB	JP75SBC50R-L20
	1 5/16"	BCH21-C2	CAT21BCB	JP131SBC50R-L20
	2"	BCH32-C2	CAT32BCB	JP2SBC50R-L20
	4"	BCH64-C2	CAT64BCB	JP4SBC50R-X20
For use with flanges up to 3/4" thick, rotates 360 degrees	3/4"	BCH12-C442	CAT12BC200B	JP75SBC87R-L20
	1 5/16"	BCH21-C442	CAT21BC200B	JP131SBC87R-L20
	2"	BCH32-C442	CAT32BC200B	JP2SBC87R-L20
	4"	BCH64-C442	CAT64BC200B	JP4SBC87R-X20

Hammer-On Beam Clamp

For use with flanges 1/8" – 1/4" thick, rotates 360 degrees	3/4"	BCH12-E-2-4	CAT1224SM	JP75HBC25R-L20
	3/4"	BCH12-U-2-4	CAT1224	JP131HBC25R-L20
	1 5/16"	BCH21-U-2-4	CAT2124	
	1 5/16"	BCH21-E-2-4	CAT2124SM	JP2HBC25R-L20
	2"	BCH32-E-2-4	CAT3224SM	
	2"	BCH32-U-2-4	CAT3224	
	4"	BCH64-E-2-4	CAT6424SM	
	For use with flanges 5/16" – 1/2" thick, rotates 360 degrees	3/4"	BCH12-E-5-8	CAT1258SM
3/4"		BCH12-U-5-8	CAT1258	JP131HBC50R-L20
1 5/16"		BCH21-E-5-8	CAT2158SM	
1 5/16"		BCH21-U-5-8	CAT2158	JP2HBC50R-L20
2"		BCH32-E-5-8	CAT3258SM	
2"		BCH32-U-5-8	CAT3258	
4"		BCH64-E-5-8	CAT6458SM	
For use with flanges 9/16" – 3/4" thick, rotates 360 degrees		3/4"	BCH12-E-9-12	CAT1291SM
	3/4"	BCH12-U-9-12	CAT12912	JP131HBC75R-L20
	1 5/16"	BCH21-E-9-12	CAT21912SM	
	1 5/16"	BCH21-U-9-12	CAT21912	JP2HBC75R-L20
	2"	BCH32-E-9-12	CAT32912SM	
	2"	BCH32-U-9-12	CAT32912	
	4"	BCH64-E-9-12	CAT64912SM	
	4"	BCH64-U-9-12	CAT64912	JP4HBC75R-X20



Cable Accessories for Building and Construction



J-Pro™ System Description	Hook Size	B-Line	ERICO (CADDY*)	Panduit
Under Floor Pedestal Support Clamp				
For use with pedestal support 7/8" square or 1 1/8" – 1 3/8" in diameter	3/4"	BCH12-L1410	CAT12CD1B	JP75UF100-L20
	1 5/16"	BCH21-L1410	CAT21CD1B	JP131UF100-L20
	2"	BCH32-L1410	CAT32CD1B	JP2UF100-L20
	4"	BCH64-L1410	CAT64CD1B	JP4UF100-X20



Description	B-Line	ERICO (CADDY*)	Panduit
Low Voltage Integral Mounting Bracket			
Single gang stud bracket	BB15	MP1S	LV-S-1G
Double gang stud bracket	BB45-08	MP2S	LV-S-2G



Description	B-Line	ERICO (CADDY*)	Panduit
Low Voltage Retrofit Mounting Plate Brackets			
Single gang wall bracket with screws	BB10L	MPLS	LV-W-1G
Double gang wall bracket with screws	BB20L	MPLS2	LV-W-2G



Description	B-Line	ERICO (CADDY*)	Panduit
Metal Stud Grommets and Punch Tool			
Metal stud grommet	BM1	ESG1	MSG-1.3-C
	BM2		
	N/A	ESGP	MSGV-1.3-C
Metal stud punch	BT25	MSP20	MSPT-1.3



Description	B-Line	ERICO (CADDY*)	Panduit
Cable Manager			
Cable support manager	BRC1	CG4	CSM-1.25-C



Description	B-Line	ERICO (CADDY*)	Panduit
Multi-Purpose Clip			
Accommodates beam flange from 1/8" to 1/2", standard 1/4 – 20 or #10 – 24 threaded bridle rings, standard drive rings as well as unthreaded bridle rings	N/A	2FMP28	BR-MPCL



Thread Size	Ring Size	B-Line	ERICO (CADDY*)	Panduit
Bridle Rings (not recommended for high performance cable)				
#8 wire (.162)	1/2"	BR-12	2BR8	BR-.50
	3/4"	BR-12	2BR12	BR-.75
	1 1/4"	BR-32	2BR20	BR-1.25
	2"	BR-32	2BR32	BR-2.0
10 – 24 threaded	1/2"	BR-8-T	2BRT8	BR-.50-10-24
	3/4"	BR-12-T	2BRT12	BR-.75-10-24
	1 1/4"	BR-20-T	2BRT20	BR-1.25-10-24
	2"	BR-32-T	2BRT32	BR-2.0-10-24
1/4" – 20 threaded	1 1/4"	BR-20-4T	4BRT20	BR-1.25-1/4-20
	2"	BR-32-4T	4BRT32	BR-2.0-1/4-20
	4"	BR-64-4T	4BRT64	BR-4.0-1/4-20
#14 wood screw thread	1 1/4"	BR-24-4W	4BRT20WS	BR-1.25-14WS
	2"	BR-32-4W	4BRT32WS	BR-2.0-14WS
Direct mount with drive pin and washer attached; can be installed with a standard powder actuated tool/gun	1 1/2"	N/A	N/A	BR-1.5-PAF
	2"	N/A	N/A	BR-2.0-PAF
Open mounting for screws, nails or other fasteners	1 1/2"	N/A	N/A	BR-1.5-SN
	2"	N/A	N/A	BR-2.0-SN
Includes integrated toggle screw	1 1/2"	N/A	N/A	BR-1.5-TW
	2"	N/A	N/A	BR-2.0-TW

*CADDY is a registered trademark of ERICO International Corporation.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300 and reference WACR13

Unified Physical Infrastructure



©2011 Panduit Corp.
ALL RIGHTS RESERVED.
Printed in the U.S.A.

SA-WACR13
Replaces SA-WACR09
6/2011