

PCD Series Plastic Cable Ducts



EXCEPTIONAL SUPPORT & PROTECTION™

Cost effective solution for open racks

Features

- Available in 11/2", 2", 3", and 4" widths
- Available in 3" and 4" depths, single channel and 6" and 8" depths dual channel
- Slotted finger design allows for horizontal cable access exactly where it's needed
- Includes mounting hardware
- Also available as raw duct without mounting ears (1.5" width)
- Fingers can be easily removed to create larger openings
- Hinged plastic covers provide organization while keeping cables hidden
- Ideal for medium to low density installations
- Can be mounted in-between racks for 38 space and higher



PCD shown on RLA series 2 post rack

Architects and Engineers' Specifications

PCD Series Plastic Cable Duct shall be Middle Atlantic Products model # PCD-__ (refer to chart). PCD shall be constructed of interior grade rigid PVC and include a hinged plastic cover. PCD shall dimensions shall be _"H x _"D x _"W (refer to chart). PCD shall be RoHS EU Directive 2002/95/EC compliant. PCD shall be manufactured by an ISO 9001 and ISO 14001 registered company. PCD shall be warrantied to be free from defects in material and workmanship under normal use and conditions for the lifetime of the product.

PCD Series Plastic Cable Ducts dimensions

PCD SINGLE WITHOUT COVER


PCD SINGLE WITH COVER


full length steel backing for added strength


user installed bracket

— (3" and 4" widths)
for mounting in-between
two racks (4 places)

All dimensions in inches unless otherwise noted [All dimensions in brackets are in millimeters]







PCD-1.5-4-4BK**	PCD-1.5-2-4BK**	PCD-2-3-30SC*	PCD-2-3-25SC*	PCD-2-3-20SC*	PCD-2-3-15SC*	PCD-2-3-12SC*	PCD-2-3-8SC*	PCD SERIES SINGLE
72 [1828.8]	72 [1828.8]	56 [1422.4]	44 [1117.6]	36 [915]	28 [711.2]	24 [610]	16 [406.4]	A LENGTH
1.5 [38.1]	1.5 [38.1]	2 [50.8]	2 [50.8]	2 [50.8]	2 [50.8]	2 [50.8]	2 [50.8]	B WIDTH
4.00 [101.60]	2.00 [50.80]	3.06 [77.72]	3.06 [77.72]	3.06 [77.72]	3.06 [77.72]	3.06 [77.72]	3.06 [77.72]	C HEIGHT

.5-4-4BK**	.5-2-4BK**	-3-30SC*	-3-25SC*	-3-20SC*	-3-15SC*	-3-12SC*	-3-8SC*	SERIES NGLE
72 [1828.8]	72 [1828.8]	56 [1422.4]	44 [1117.6]	36 [915]	28 [711.2]	24 [610]	16 [406.4]	A LENGTH
1.5 [38.1]	1.5 [38.1]	2 [50.8]	2 [50.8]	2 [50.8]	2 [50.8]	2 [50.8]	2 [50.8]	B WIDTH
4.00 [101.60]	2.00 [50.80]	3.06 [77.72]	3.06 [77.72]	3.06 [77.72]	3.06 [77.72]	3.06 [77.72]	3.06 [77.72]	C HEIGHT

does not include brackets, includes mounting hardware.
 does not include brackets, does not include mounting hardware, includes 4 pieces



-PCDB-90-1,5-12 optional mounting bracket to orient duct 90 optional mounting bracket to orient duct 90 for use with PCD-1,5-2-4BK & PCD-1,5-4BK only includes 12 brackets

œ