

SVS-5R

RAID 5 HDD Extension Unit



SVS-5R

Key Features

SVS-5R

- 1U 19-inch rack case
- Data transmission speed : Up to 3.0Gbps (SATA II)
- Available SATA HDD : Up to 4 (4TB)

Technical Specifications

	SVS-5R
Transmission Speed	Up to 3.0Gbps (SATA II)
Maximum Capacity	Up to 4TB
Internal HDD	Up to 4 SATA HDDs
RAID	RAID 0, 1, 0+1, 5
eSATA	1 External SATA ports for DVR connection
USB	USB 2.0, RAID configuration only
Operating Temperature	+5°C ~ +45°C (+41°F ~ +113°F)
Operating Humidity	20% ~ 70% RH
Input Voltage	115 ~ 230V AC ±10%, 50/60Hz, Autoranging
Dimensions (WxHxD)	482.0 x 44.0 x 433.0mm (19" x 1.7" x 17")
Weight	Approx. 6.4Kg (14.1 lb)
Rack Mount Kit	For mounting one unit in an EIA 19-inch rack
Certifications	FCC (Class A), UL/cUL listed, CE (Class A)

Dimensions

Unit : mm (inch)

SVS-5R

