

Screw-Cover Type 3R Boxes and Enclosures

Screw-Cover, Type 3R



Industry Standards

UL 50, 50E Listed; Type 3R; File No. E27525
cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA/EEMAC Type 3R
IEC 60529, IP32

Application

Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Features

- Drip shield top and seam-free sides, front and back
- Slip-on removable cover fastened with plated steel screws along bottom edge
- Handles on larger sizes (see table)
- Embossed mounting holes on back of enclosure
- Knockouts in bottom of 16 and 14 gauge enclosures
- Provision for padlocking
- No gasketing

Specifications

- 16, 14 or 12 gauge galvanized steel

Finish

ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.

Accessories

See also *Accessories*.
Industrial Corrosion Inhibitors
Electric Heater
Grounding Device
Mounting Bracket Kit
Touch-Up Paint

Bulletin: A90S3

Standard Product

Catalog Number	AxBxC in./mm	Body Style	D in./mm	Mounting H in./mm	Mounting J in./mm	Knockout Pattern
A4R44	4.00 x 4.00 x 4.00	A	—	1.88	2.00	B-C
	102 x 102 x 102		—	48	51	
A6R44	6.00 x 4.00 x 4.00	A	—	1.88	1.06	B-C
	152 x 102 x 102		—	48	27	
A12R44	12.00 x 4.00 x 4.00	A	—	1.88	1.06	B-C
	305 x 102 x 102		—	48	27	
A6R64	6.00 x 6.00 x 4.00	A	—	2.25	1.06	B-C-D
	152 x 152 x 102		—	57	27	
A8R64	8.00 x 6.00 x 4.00	A	—	2.25	1.06	B-C-D
	203 x 152 x 102		—	57	27	
A8R84	8.00 x 8.00 x 4.00	A	—	2.25	1.06	F-G-H-I
	203 x 203 x 102		—	57	27	
A10R84	10.00 x 8.00 x 4.00	A	—	2.25	1.06	F-G-H-I
	254 x 203 x 102		—	57	27	
A12R84	12.00 x 8.00 x 4.00	A	—	2.25	1.06	F-G-H-I
	305 x 203 x 102		—	57	27	
A10R104	10.00 x 10.00 x 4.00	A	—	2.25	1.06	C-D-E-F-G
	254 x 254 x 102		—	57	27	
A12R104	12.00 x 10.00 x 4.00	A	—	2.25	1.06	C-D-E-F-G
	305 x 254 x 102		—	57	27	
A12R124	12.00 x 12.00 x 4.00	A	—	2.25	1.06	C-D-E-F-G
	305 x 305 x 102		—	57	27	
A18R124	18.00 x 12.00 x 4.00	A	—	2.25	1.06	C-D-E-F-G
	457 x 305 x 102		—	57	27	
A18R184	18.00 x 18.00 x 4.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	457 x 457 x 102		—	330	28	
A6R66	6.00 x 6.00 x 6.00	A	—	2.25	1.06	B-C-D
	152 x 152 x 152		—	57	27	
A8R86	8.00 x 8.00 x 6.00	A	—	2.25	1.06	F-G-H-I
	203 x 203 x 152		—	57	27	
A10R86	10.00 x 8.00 x 6.00	A	—	2.25	1.06	F-G-H-I
	254 x 203 x 152		—	57	27	
A10R106	10.00 x 10.00 x 6.00	A	—	2.25	1.06	C-D-E-F-G
	254 x 254 x 152		—	57	27	
A12R86	12.00 x 8.00 x 6.00	A	—	2.25	1.06	F-G-H-I
	305 x 203 x 152		—	57	27	
A12R106	12.00 x 10.00 x 6.00	A	—	2.25	1.06	C-D-E-F-G
	305 x 254 x 152		—	57	27	
A12R126	12.00 x 12.00 x 6.00	A	—	2.25	1.06	C-D-E-F-G
	305 x 305 x 152		—	57	27	
A15R126	15.00 x 12.00 x 6.00	A	—	2.25	1.06	C-D-E-F-G
	381 x 305 x 152		—	57	27	

Screw-Cover Type 3R Boxes and Enclosures

Catalog Number	AxBxC in./mm	Body Style	D in./mm	Mounting H in./mm	Mounting J in./mm	Knockout Pattern
A16R126	16.00 x 12.00 x 6.00	A	—	2.25	1.06	C-D-E-F-G
	406 x 305 x 152		—	57	27	
A18R126	18.00 x 12.00 x 6.00	A	—	2.25	1.06	C-D-E-F-G
	457 x 305 x 152		—	57	27	
A18R186	18.00 x 18.00 x 6.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	457 x 457 x 152		—	330	28	
A24R126	24.00 x 12.00 x 6.00	B	—	13.00	1.12	C-D-E-F-G
	610 x 305 x 152		—	330	28	
A24R186	24.00 x 18.00 x 6.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	610 x 457 x 152		—	330	28	
A24R246	24.00 x 24.00 x 6.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	610 x 610 x 152		—	330	28	
A8R88	8.00 x 8.00 x 8.00	A	—	2.25	1.06	F-G-H-I
	203 x 203 x 203		—	57	27	
A12R128	12.00 x 12.00 x 8.00	A	—	2.25	1.06	C-D-E-F-G
	305 x 305 x 203		—	57	27	
A15R128	15.00 x 12.00 x 8.00	A	—	2.25	1.06	C-D-E-F-G
	381 x 305 x 203		—	57	27	
A18R128	18.00 x 12.00 x 8.00	A	—	2.25	1.12	C-D-E-F-G
	457 x 305 x 203		—	57	28	
A24R168	24.00 x 16.00 x 8.00	B	—	13.00	1.12	C-D-E-F-G
	610 x 407 x 203		—	330	28	
A18R188	18.00 x 18.00 x 8.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	457 x 457 x 203		—	330	28	
A24R188	24.00 x 18.00 x 8.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	610 x 457 x 203		—	330	28	
A24R208	24.00 x 20.00 x 8.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	610 x 508 x 203		—	330	28	
A24R248	24.00 x 24.00 x 8.00	C	12.19	13.00	1.12	A-B-C-D-E-F-G-H-I
	610 x 610 x 203		310	330	28	
A30R248	30.00 x 24.00 x 8.00	C	15.19	13.00	1.12	A-B-C-D-E-F-G-H-I
	762 x 610 x 203		386	330	28	
A48R368	48.00 x 36.00 x 8.00	C	24.19	33.00	1.50	A-B-C-D-E-F-G-H-I
	1219 x 914 x 203		614	838	38	
A18R1810	18.00 x 18.00 x 10.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	457 x 457 x 254		—	330	28	
A24R1810	24.00 x 18.00 x 10.00	B	—	13.00	1.12	A-B-C-D-E-F-G-H-I
	610 x 457 x 254		—	330	28	
A24R2410	24.00 x 24.00 x 10.00	C	12.19	13.00	1.12	A-B-C-D-E-F-G-H-I
	610 x 610 x 254		310	330	28	
A30R2410	30.00 x 24.00 x 10.00	C	15.19	13.00	1.50	A-B-C-D-E-F-G-H-I
	762 x 610 x 254		386	330	38	
A24R2412	24.00 x 24.00 x 12.00	C	12.19	13.00	1.12	A-B-C-D-E-F-G-H-I
	610 x 610 x 305		310	330	28	
A30R3012	30.00 x 30.00 x 12.00	C	15.19	27.00	1.50	A-B-C-D-E-F-G-H-I
	762 x 762 x 305		386	686	38	
A36R3012	36.00 x 30.00 x 12.00	C	18.19	27.00	1.50	A-B-C-D-E-F-G-H-I
	914 x 762 x 305		462	686	38	
A36R3612	36.00 x 36.00 x 12.00	C	18.19	33.00	1.50	A-B-C-D-E-F-G-H-I
	914 x 914 x 305		462	838	38	
A30R3016	30.00 x 30.00 x 16.00	C	15.19	27.00	1.50	A-B-C-D-E-F-G-H-I
	762 x 762 x 406		386	686	38	
A48R3616	48.00 x 36.00 x 16.00	C	24.19	33.00	1.50	A-B-C-D-E-F-G-H-I
	1219 x 914 x 406		614	838	38	
A4R44NK	4.00 x 4.00 x 4.00	A	—	1.88	2.00	—
	102 x 102 x 102		—	48	51	
A6R64NK	6.00 x 6.00 x 4.00	A	—	2.25	1.06	—
	152 x 152 x 102		—	57	27	
A8R64NK	8.00 x 6.00 x 4.00	A	—	2.25	1.06	—
	203 x 152 x 102		—	57	27	
A8R84NK	8.00 x 8.00 x 4.00	A	—	2.25	1.06	—
	203 x 203 x 102		—	57	27	
A10R84NK	10.00 x 8.00 x 4.00	A	—	2.25	1.06	—
	254 x 203 x 102		—	57	27	
A12R84NK	12.00 x 8.00 x 4.00	A	—	2.25	1.06	—
	305 x 203 x 102		—	57	27	
A10R104NK	10.00 x 10.00 x 4.00	A	—	2.25	1.06	—
	254 x 254 x 102		—	57	27	
A12R104NK	12.00 x 10.00 x 4.00	A	—	2.25	1.06	—
	305 x 254 x 102		—	57	27	
A12R124NK	12.00 x 12.00 x 4.00	A	—	2.25	1.06	—
	305 x 305 x 102		—	57	27	
A18R184NK	18.00 x 18.00 x 4.00	B	—	13.00	1.12	—
	457 x 457 x 102		—	330	28	
A6R66NK	6.00 x 6.00 x 6.00	A	—	2.25	1.06	—
	152 x 152 x 152		—	57	27	

Screw-Cover Type 3R Boxes and Enclosures

Catalog Number	AxBxC in./mm	Body Style	D in./mm	Mounting H in./mm	Mounting J in./mm	Knockout Pattern
A18R66NK	18.00 x 6.00 x 6.00	A	—	2.25	1.06	—
	457 x 152 x 152			57	27	
A8R86NK	8.00 x 8.00 x 6.00	A	—	2.25	1.06	—
	203 x 203 x 152			57	27	
A10R86NK	10.00 x 8.00 x 6.00	A	—	2.25	1.06	—
	254 x 203 x 152			57	27	
A10R106NK	10.00 x 10.00 x 6.00	A	—	2.25	1.06	—
	254 x 254 x 152			57	27	
A12R106NK	12.00 x 10.00 x 6.00	A	—	2.25	1.06	—
	305 x 254 x 152			57	27	
A12R126NK	12.00 x 12.00 x 6.00	A	—	2.25	1.06	—
	305 x 305 x 152			57	27	
A15R126NK	15.00 x 12.00 x 6.00	A	—	2.25	1.06	—
	381 x 305 x 152			57	27	
A16R126NK	16.00 x 12.00 x 6.00	A	—	2.25	1.06	—
	406 x 305 x 152			57	27	
A18R126NK	18.00 x 12.00 x 6.00	A	—	2.25	1.06	—
	457 x 305 x 152			57	27	
A18R186NK	18.00 x 18.00 x 6.00	B	—	13.00	1.12	—
	457 x 457 x 152			330	28	
A24R186NK	24.00 x 18.00 x 6.00	B	—	13.00	1.12	—
	610 x 457 x 152			330	28	
A24R246NK	24.00 x 24.00 x 6.00	B	—	13.00	1.12	—
	610 x 610 x 152			330	28	
A8R88NK	8.00 x 8.00 x 8.00	A	—	2.25	1.06	—
	203 x 203 x 203			1.06	27	
A24R88NK	24.00 x 8.00 x 8.00	A	—	2.25	1.06	—
	610 x 203 x 203			1.06	27	
A12R128NK	12.00 x 12.00 x 8.00	A	—	2.25	1.06	—
	305 x 305 x 203			57	27	
A15R128NK	15.00 x 12.00 x 8.00	A	—	2.25	1.06	—
	381 x 305 x 203			57	27	
A18R128NK	18.00 x 12.00 x 8.00	A	—	2.25	1.12	—
	457 x 305 x 203			57	28	
A18R188NK	18.00 x 18.00 x 8.00	B	—	13.00	1.12	—
	457 x 457 x 203			330	28	
A24R188NK	24.00 x 18.00 x 8.00	B	—	13.00	1.12	—
	610 x 457 x 203			330	28	
A24R208NK	24.00 x 20.00 x 8.00	B	—	13.00	1.12	—
	610 x 508 x 203			330	28	
A24R248NK	24.00 x 24.00 x 8.00	C	12.19	13.00	1.12	—
	610 x 610 x 203		310	330	28	
A30R248NK	30.00 x 24.00 x 8.00	C	15.19	13.00	1.12	—
	762 x 610 x 203		386	330	28	
A48R368NK	48.00 x 36.00 x 8.00	C	24.19	33.00	1.50	—
	1220 x 915 x 203		614	838	38	
A24R2410NK	24.00 x 24.00 x 10.00	C	12.19	13.00	1.12	—
	610 x 610 x 254		310	330	28	
A24R2412NK	24.00 x 24.00 x 12.00	C	12.19	13.00	1.12	—
	610 x 610 x 305		310	330	28	
A30R3012NK	30.00 x 30.00 x 12.00	C	15.19	27.00	1.50	—
	762 x 762 x 305		386	686	38	
A36R3012NK	36.00 x 30.00 x 12.00	C	18.19	27.00	1.50	—
	914 x 762 x 305		462	686	38	
A36R3612NK	36.00 x 36.00 x 12.00	C	18.19	33.00	1.50	—
	914 x 914 x 305		462	838	38	
A30R3016NK	30.00 x 30.00 x 16.00	C	15.19	27.00	1.50	—
	762 x 762 x 406		386	686	38	
A48R3616NK	48.00 x 36.00 x 16.00	C	24.19	33.00	1.50	—
	1219 x 915 x 406		614	838	38	

Screw-Cover Type 3R Boxes and Enclosures

