

SKINDICHT® SM-PE LOCK NUTS



Brass Grounding Lock Nuts for PG and Metric Threaded Products

SKINDICHT® SM-PE Lock Nuts are required wherever varnished, anodized and powder coated housings are used. When the lock nut is tightened, the raised edges cut through the insulating layer, guaranteeing optimum contact. Ideal for use with MS-SC cable grounding cable glands.



Technical Data:



Materials:

Nickel-Plated Brass

SKINDICHT® SM-PE: PG Brass Lock Nuts

Part Number	Thread Type & Size	Wrenching Flats		Nut Thickness		Standard Pack Size
		inches	mm	inches	mm	
52103200	PG-7	0.590	15	.185	4.7	100
52103210	PG-9	0.709	18	.185	4.7	100
52103220	PG-11	0.827	21	.185	4.7	100
52103230	PG-13	0.906	23	.185	4.7	100
52103240	PG-16	1.024	26	.185	4.7	100
52103250	PG-21	1.260	32	.205	5.2	50
52103260	PG-29	1.614	41	.224	5.7	50
52103270	PG-36	2.008	51	.264	6.7	50

SKINDICHT® SM-PE-M: Metric Brass Lock Nuts

Part Number	Thread Type & Size	Wrenching Flats		Nut Thickness		Standard Pack Size
		inches	mm	inches	mm	
52103300	M-12X1.5	0.591	15	0.138	3.5	100
52103310	M-16X1.5	0.748	19	0.138	3.5	100
52103320	M-20X1.5	0.945	24	0.146	3.7	100
52103330	M-25X1.5	1.181	30	0.165	4.2	50
52103340	M-32X1.5	1.417	36	0.185	4.7	50
52103350	M-40X1.5	1.811	46	0.217	5.5	25
52103360	M-50X1.5	2.362	60	0.217	5.5	10
52103370	M-63X1.5	2.756	70	0.276	7.0	10
52103371	M-75X1.5	2.953	75	0.315	8.0	5
52103372	M-90X2.0	4.016	102	0.394	10.0	1
52103373	M-110X2.0	4.882	124	0.472	12.0	1