



PE 961 POCKET GUIDE



Talk Mode

Press to go off-hook. A double beep & flashing red LED indicates this mode. This test set will then automatically perform the following line checks:

1. Digital Signal Presence: 2-Tone alarm & lockout. To override, hold down TALK key for 6 seconds.



2. High DC (>116V): Single Tone & lockout. No override capability.



3. High DC (76V-116V): Single-tone & flashing red/green LED. Override by holding TALK key until alarm clears.



Monitor Mode



Mute Mode

Press & release MUTE to cut off or disable transmission (speech). Press again to talk.



Pulse Dialing



Storing Numbers

While connected to a circuit & in the off-hook mode:

1. Press STO
2. Press MEM and a location (0-9).
3. Enter the telephone number to be stored.
4. Press STO to store.



Dialing A Stored Number

Press MEM, then the digit (0-9) where the desired number is stored.

Stored Numbers

0: _____	5: _____
1: _____	6: _____
2: _____	7: _____
3: _____	8: _____
4: _____	9: _____



Last Number Redial & Pause



Flash



Speaker

1. ONE-WAY (Receive Only): While in the TALK mode, press SPKR. The Mute function is automatically activated.
2. TWO-WAY HANDS FREE: While in the Talk mode, press SPKR, then press Mute.
3. MONITOR ONLY: While in the OFF (on hook) mode, press and release SPKR to select Monitor mode without the loudspeaker.



Volume Control



Polarity Test

(Press) to determine polarity.

Green LED: Red wire to Ring.

Red LED: Red wire to Tip.



Low Battery

