

Part Number: VRTB200-10210

Basic, Non-Surge

Power Configuration: 20A, 120V, 1.9kW

Physical Configuration: 66 in Vertical



Description:

The VRTB200-10210 non-surge unit is ideal for facilities already equipped with surge protection.

Product Highlights:

Monitoring: None

Plug Form:  5-20P

Receptacle: (Type & Qty)  NEMA 5-20R - Qty: 20

**POWER****GEIST****Part Number: VRTB200-10210****Product Specifications and Options:**

Quantity Of Inputs	1
Voltage	120V
Amperage	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	20 AMP Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
Quantity on Face #1	20
Quantity per Breaker #1	20
Style #1	Duplex
Maximum Output per Receptacle/Socket #1	20A
Voltage per Receptacle/Socket #1	120V
Heavy Steel -Black Powder Coat	Yes
Configuration	66in Vertical Rackmount
Full Length Bracket	Yes
SLB-4 Brackets	Optional
EZB-1 Brackets	Optional
XB-7 Brackets	Optional
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 1.85in x 1.30in
Shipping Weight	12 lbs

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza, Unit #2808,
No. 195 Haide 3 Road
Nanshan District,
Shenzhen
Guangdong Province
P. R. China
Postal Code: 518000
Tel: +86.755.8663.9505

Geist Asia

Hong Kong
Tel: +85 2903 619 27
Email: salesasia@geistglobal.com