

Lens	Camera Model	Lens Format	HFOV Telephoto	HFOV Wide	MM Rating	F-Stop	Iris Operation	Day/Night	Lens Mount
V6	IQ761, IQ861	1/2"	7°	23°	12-40mm	F1.8	Manual	Yes	CS
	IQ762, IQ862	1/2"	9°	28°	12-40mm	F1.8	Manual	Yes	CS
	IQ763, IQ863	1/2"	9°	25°	12-40mm	F1.8	Manual	Yes	CS
	IQ765, IQ865	1/2"	9°	28°	12-40mm	F1.8	Manual	Yes	CS
V7	IQ861	1/2"	31°	75°	4-12mm	F1.4	Manual	Yes	CS
	IQ862	1/2"	27°	63°	4-12mm	F1.4	Manual	Yes	CS
	IQ863	1/2"	25°	58°	4-12mm	F1.4	Manual	Yes	CS
	IQ765, IQ865	1/2"	30°	74°	4-12mm	F1.4	Manual	Yes	CS
V11	IQ030	1/3"	22°	49°	3.5-9mm	F1.6	Manual	No	CS
	IQ031	1/3"	31°	70°	3.5-9mm	F1.6	Manual	No	CS
	IQ032	1/3"	41°	94°	3.5-9mm	F1.6	Manual	No	CS
V16	IQ761	1/3"	28°	89°	2.8-12mm	F1.4	Manual	Yes	CS
	IQ762	1/3"	33°	100°	2.8-12mm	F1.4	Manual	Yes	CS
	IQ763	1/3"	32°	103°	2.8-12mm	F1.4	Manual	Yes	CS
B5	IQA30N	1/3"	27°	76°	3-13mm	F1.4	Fixed	Yes	M14
	IQA31N	1/3"	27°	76°	3-13mm	F1.4	Fixed	Yes	M14
	IQA32N	1/3"	32°	94°	3-13mm	F1.4	Fixed	Yes	M14
	IQA33N	1/3"	26°	71°	3-13mm	F1.4	Fixed	Yes	M14
	IQM30N	1/3"	27°	76°	3-13mm	F1.4	Fixed	Yes	M14
	IQM31N	1/3"	27°	76°	3-13mm	F1.4	Fixed	Yes	M14
	IQM32N	1/3"	32°	94°	3-13mm	F1.4	Fixed	Yes	M14
B6	IQA35N	1/2"	34°	90°	3.3-12mm	F1.4	Fixed	Yes	M14
W2	IQ762, IQ862	1/2"	87°	115°	1.8-3mm	F1.8	Manual	Yes	CS
	IQ763, IQ863	1/2"	87°	115°	1.8-3mm	F1.8	Manual	Yes	CS
	IQ765, IQ865	1/2"	87°	115°	1.8-3mm	F1.8	Manual	Yes	CS
F1	IQD30S	1/3"	48°		4.2mm	F1.8	Fixed	No	M12
	IQD31S	1/3"	48°		4.2mm	F1.8	Fixed	No	M12
	IQD32S	1/3"	65°		4.2mm	F1.8	Fixed	No	M12
F2	IQD30S	1/3"	58°		2.8mm	F2.6	Fixed	No	M12
	IQD31S	1/3"	86°		2.8mm	F2.6	Fixed	No	M12
F3	IQD30S	1/3"	20°		8.0mm	F1.8	Fixed	No	M12
	IQD31S	1/3"	31°		8.0mm	F1.8	Fixed	No	M12
	IQD32S	1/3"	28°		8.0mm	F1.8	Fixed	No	M12
F4	IQD32S	1/3"	95°		3.6mm	F1.8	Fixed	No	M12

www.iqeye.com

IQinVision, Inc.
33122 Valle Road
San Juan Capistrano, CA 92675
+1 949.369.8100