


FINISHED WIRE DATA		
CONDUCTORS	WIRE AWG	24 AWG
	MATERIAL	SOLID BARE COPPER
INSULATION	MATERIAL	POLYOLEFIN & FLUOROPOLYMER
JACKET	MATERIAL	FR PVC
FILLER	MATERIAL	POLYOLEFIN

COLOR CODE	
PAIR COLOR CODE	
1	WHT-BLU/BLU
2	WHT-ORG/ORG
3	WHT-GRN/GRN
4	WHT-BRN/BRN




LEGEND TO BE REPEATED EVERY 24"

TE CONNECTIVITY 640 SERIES 4/24 AWG T256 F/UTP CMR C(UL)US CAT 6 PAT 6153826, 6150612 XXXX FT

LOC	DIST	REVISIONS					
EH	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P	REV ECO-12-012939	17JUL2012	GG	SS

- 1
- SEQUENTIAL FOOTAGE RETURNED TO ZERO FOR EACH LENGTH.
ON PUTUP LENGTHS 3000 FT OR LESS.
- 2
- INSULATION COLORS SHALL BE BLUE, ORANGE, GREEN,
BROWN AND WHITE, WITH CORRESPONDING STRIPES.
THE INSULATION COLOR MAY BE TRANSLUCENT.
- 3
- XX = JACKET COLOR - BL = BLUE, WT = WHITE, GY = GRAY,
GN = GREEN, YL = YELLOW, OR = ORANGE, RD = RED, VT = VIOLET,
BK = BLACK.
- 4
- PRINT COLOR SHALL BE DARK BLUE, EXCEPT WHITE ON BLACK JACKET.
- 5
- DATE CODE.
- 6
- GOVERNING SPECIFICATIONS - LATEST REVISIONS
NEC 800
UL444 CMR
TIA 568-C.2 CAT 6A
- 7
- REPLACE "02" FOR THE FOLLOWING FOOTAGES:
04=2000', 05=2500', CALL FOR ADDITIONAL OPTIONS.

CATALOG NUMBER	WEIGHT		PACKAGING
	LBS/KFT	KG/KM	
TE64DRF-XX02	48	71	1,000' REEL



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L. HALL 22OCT03		 TE Connectivity				
DIMENSIONS: INCHES			CHK R.SPEER 24OCT03						
			APVD R.SPEER 24OCT03		NAME CABLE, 640 SERIES, CATEGORY 6A, XG SYSTEM, 4 FTP, CMR —				
			PRODUCT SPEC —						
			APPLICATION SPEC —						
			WEIGHT —						
MATERIAL —			FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C=1499389	RESTRICTED TO —	
CUSTOMER DRAWING					SCALE NTS	SHEET 1 of 1		REV P	