




LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A	REVISED PER EC 0S13-0266-05	18JUL06	BM	CR



1. CONTACTS ACCEPT 20-24 AWG RANGE.
- ⚠ INSERTS: NYLON, GLASS FILLED, UL 94V-0 RATED, BLACK.
- ⚠ CABLE CLAMP & CABLE GATE PLUG: POLYPROPYLENE, BLACK
- ⚠ CONTACTS: PHOSPHOR BRONZE.
- ⚠ SHELLS: CARBON STEEL.
- ⚠ CABLE GATE PLUG TO BE PLACED IN CABLE EXIT NOT BEING USED.
- ⚠ CONTACTS: GOLD FLASH FOR A LENGTH OF 2.54[.100] MIN FROM MATING END, 2.54µm[.000100] MIN TIN ON OPPOSITE END FOR A LENGTH OF 4.06 [.160] MIN FROM END OF INSULATION BARREL, BOTH OVER 0.76µm[.000030] MIN NICKEL ON ENTIRE CONTACT.
- ⚠ SHELLS: 5.08µm[.000200] MIN TIN OVER 2.54µm[.000100] MIN COPPER.
- ⚠ STRAIN RELIEF CLIP CAN BE REVERSED FOR PROPER INSTALLATION, DEPENDING ON SIZE OF CABLE DIAMETER.
- ⚠ STRAIN RELIEF CLIP AND SELF TAPPING SCREWS MAY BE USED AT EITHER CABLE EXIT.
11. CABLE DIAMETER RANGE = 4.58-11.68 [.180-.460].



THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	12-22-04	tyco Electronics				Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
				CHK	12-22-04								
				APVD	12-22-04	NAME				RECEPTACLE KIT, UNASSEMBLED, SIZE 3, 25 POSITION, AMPLIMITE HDP-20			
				PRODUCT SPEC		108-40005		APPLICATION SPEC		114-10000 & 114-40030		WEIGHT	
				CUSTOMER DRAWING		SCALE		3:1		SHEET		1 OF 1	