



LOC	DIST	REVISIONS						
HM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			B	REV: ECO-10-013830	02JUL2010	GG	DC	
			C	REV ECO-10-017340	24AUG2010	LH	DC	
			C1	ADD DASH NO. REV ECO-11-016961	22AUG2011	LH	SJ	

1. CABLE ASSEMBLY 100% TESTED FOR OPENS AND SHORTS [300 VDC HIPOT], AND WIRING DIAGRAM.

△₂ ONE LABEL APPLIED FOR LENGTHS UP TO 4 METERS.
TWO LABELS APPLIED FOR LENGTHS FOR 5 METERS AND GREATER.



30±0.300	[98.43±0.98]	3-1933960-0
29±0.200	[95.15±0.66]	2-1933960-9
28±0.200	[91.87±0.66]	2-1933960-8
27±0.200	[88.59±0.66]	2-1933960-7
26±0.200	[85.31±0.66]	2-1933960-6
25±0.200	[82.03±0.66]	2-1933960-5
24±0.100	[78.74±0.33]	2-1933960-4
23±0.100	[75.46±0.33]	2-1933960-3
22±0.100	[72.18±0.33]	2-1933960-2
21±0.100	[68.90±0.33]	2-1933960-1
20±0.100	[65.62±0.33]	2-1933960-0
19±0.100	[62.34±0.33]	1-1933960-9
18±0.100	[59.06±0.33]	1-1933960-8
17±0.100	[55.78±0.33]	1-1933960-7
16±0.100	[52.50±0.33]	1-1933960-6
15±0.100	[49.22±0.33]	1-1933960-5
14±0.100	[45.93±0.33]	1-1933960-4
13±0.100	[42.65±0.33]	1-1933960-3
12±0.075	[39.37±0.25]	1-1933960-2
11±0.075	[36.09±0.25]	1-1933960-1
10±0.075	[32.81±0.25]	1-1933960-0
9±0.075	[29.53±0.25]	1933960-9
8±0.075	[26.25±0.25]	1933960-8
7±0.075	[22.97±0.25]	1933960-7
6±0.075	[19.69±0.25]	1933960-6
5±0.075	[16.41±0.25]	1933960-5
4±0.075	[13.12±0.25]	1933960-4
3±0.050	[9.84±0.16]	1933960-3
2±0.050	[6.56±0.16]	1933960-2
L — METERS [FEET]		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 09MAR2010 CHG D. CRAIG 09MAR2010 APVD D. CRAIG 09MAR2010		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CABLE ASSY, MRJ 21/MRJ 21 LIMITED DISTANCE GIGABIT ETHERNET, GRAY, CMR, REDUCED DIAMETER -	

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REV

DATE

BY

CHK

DATE

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

EH

00

1

00779

1933960

C1

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

-

-

-

MRJ 21

MRJ 21

MRJ 21

MRJ 21

1

WHT/BLU

1

2

BLU/WHT

2

13

WHT/ORG

13

14

ORG/WHT

14

3

WHT/GRN

3

4

GRN/WHT

4

15

WHT/BRN

15

16

BRN/WHT

16

25

WHT/GRY

25

26

GRY/WHT

26

37

RED/BLU

37

38

BLU/RED

38

27

RED/ORG

27

28

ORG/RED

28

39

RED/GRN

39

40

GRN/RED

40

5

RED/BRN

5

6

BRN/RED

6

17

RED/GRA

17

18

GRY/RED

18

7

BLK/BLU

7

8

BLU/BLK

8

19

BLK/ORG

19

20

ORG/BLK

20

29

BLK/GRN

29

30

GRN/BLK

30

41

BLK/BRN

41

42

BRN/BLK

42

31

BLK/GRY

31

32

GRY/BLK

32

43

YEL/BLU

43

44

BLU/YEL

44

9

YEL/ORG

9

10

ORG/YEL

10

21

YEL/GRN

21

22

GRN/YEL

22

11

YEL/BRN

11

12

BRN/YEL

12

23

YEL/GRY

23

24

GRY/YEL

24

33

VIO/BLU

33

34

BLU/VIO

34

45

VIO/ORG

45

46

ORG/VIO

46

35

VIO/GRN

35

36

GRN/VIO

36

47

VIO/BRN

47

48

BRN/VIO

48

WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

G. GARRETT

09MAR2010

CHK

D. CRAIG

09MAR2010

APVD

D. CRAIG

09MAR2010

NAME

CABLE ASSY, MRJ 21/MRJ 21, LIMITED DISTANCE,

PRODUCT SPEC

108-2064

APPLICATION SPEC

—

SIZE

A1

CAGE CODE

00779

DRAWING NO

1933960

RESTRICTED TO

—

WEIGHT

—

CUSTOMER DRAWING

SCALE

NTS

SHEET

2

OF

2

REV

C1