


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	D0		S	REV PER ECO-12-007856	25APR12	PY	RL

D



B

A

- ALL DIMENSIONS APPLY AFTER PLATING.
- THIS DRAWING COMPLIES WITH SPECIFICATION MIL-C-39029/63 AND M24308/10-1.
- ALL DIAMETERS CONCENTRIC WITH EACH OTHER WITHIN .004 T.I.R.
- POINT OF PLATING MEASUREMENT .150 [3.81] FROM WIRE BARREL END OF CONTACT.
- ALL SURFACES HAVE $\sqrt{63}$ OR BETTER FINISH.
- GOLD PLATED PER ASTM-B-488 TYPE 2, GRADE C, CLASS 1.25 OVER NICKEL PER QQ-N-290 IN MATING AREAS. GOLD PLATED PER ASTM-B-488 OVER NICKEL PER QQ-N-290 IN NON MATING AREAS.
- GOLD PLATED PER ASTM-B-488 TYPE 3, GRADE C, CLASS .75 OVER NICKEL PER QQ-N-290.
- SLEEVE MAY BE CRIMPED, DIMPLED OR PRESS FIT TO BODY
- MANUFACTURER'S LOGO ("A" OR "- . .") LOCATION OPTIONAL.

SUPERSEDED BY 1218267-3	NO	7	LOOSE PIECE	205090-7
	YES	6	TAPE MOUNTED	205090-2
	YES	6	LOOSE PIECE	205090-1
COLOR CODE		FINISH		PART NUMBER
				DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 8-17-04	TE Connectivity		
DIMENSIONS: INCHES		CHK D.MILLER 8-17-04			
		APVD D.MILLER 8-17-04	NAME		
		PRODUCT SPEC	CONTACT ASSY, SOCKET, SIZE 20,AMPLIMITE		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC			
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS	SIZE A2	CAGE CODE 00779	DRAWING NO C=205090
		WEIGHT -	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE 20:1	SHEET 1 of 1	REV S