



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
EH	00	H	REV ECO-12-007616	08MAY2012	GG JG



- ONE CABLE PACKAGED IN A CLEAR POLYBAG.
- DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- CABLE: UNSHIELDED 24 AWG, 4 TWISTED PAIRS, 7/32 STRANDED CONDUCTORS, 100 OHMS.
- DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
- AN ALTERNATE FORM OF CONNECTOR COMPONENTS RESULTING IN EQUIVALENT PERFORMANCE IS ACCEPTABLE.



0.15	0.5	203.2 (8.00)	9-219244-8
21.34	70	21488.4 (846.00)	7-219244-0
19.81	65	19964.4 (786.00)	6-219244-5
15.54	51	15697.2 (618.00)	5-219244-1
15.24	50	15392.4 (606.00)	5-219244-0
12.20	40	12344.4 (486.00)	4-219244-0
10.37	34	10515.6 (414.00)	3-219244-4
9.15	30	9296.4 (366.00)	3-219244-0
7.62	25	7721.6 (304.00)	2-219244-5
6.10	20	6197.6 (244.00)	2-219244-0
4.88	16	4978.4 (196.00)	1-219244-6
4.57	15	4724.4 (184.00)	1-219244-5
4.27	14	4368.8 (172.00)	1-219244-4
3.66	12	3759.2 (148.00)	1-219244-2
3.35	11	3454.4 (136.00)	1-219244-1
3.05	10	3149.6 (124.00)	1-219244-0
2.74	9	2794.0 (110.00)	219244-9
2.44	8	2489.2 (98.00)	219244-8
2.14	7	2184.4 (86.00)	219244-7
1.83	6	1879.6 (74.00)	219244-6
1.53	5	1574.8 (62.00)	219244-5
1.22	4	1270.0 (50.00)	219244-4
0.92	3	965.2 (38.00)	219244-3
0.61	2	660.4 (26.00)	219244-2
0.30	1	355.6 (14.00)	219244-1
METERS, REF	FEET, REF	DIM A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M. BOLES 25JUL97	Tyco Electronics Corporation Harrisburg, PA 17105-3608		
CHK B. ANTHONY 25JUL97			
APVD B. ANTHONY 25JUL97			
PRODUCT SPEC			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME B. ANTHONY	CABLE ASSEMBLY, MOD PLUG, 8 POSITION RED, ENHANCED CATEGORY 5
0 PLC ± -	1 PLC ± -	PRODUCT SPEC 108-1163	SIZE A2
2 PLC ± -	3 PLC ± -	APPLICATION SPEC 114-6053	CAGE CODE 00779
4 PLC ± -	ANGLES ± -	WEIGHT -	DRAWING NO C=219244
MATERIAL -	FINISH -	CUSTOMER DRAWING	RESTRICTED TO -
		SCALE NTS	SHEET 1 OF 1
		REV H	