



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
EH	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		G		REV: ECO-12-007616	08MAY2012	GG	JG



- ONE CABLE PACKAGED IN A CLEAR POLYBAG.
- DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- CABLE: UNSHIELDED 24 AWG, 4 TWISTED PAIRS, 7/32 STRANDED CONDUCTORS, 100 OHMS.
- DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
- AN ALTERNATE FORM OF CONNECTOR COMPONENTS RESULTING IN EQUIVALENT PERFORMANCE IS ACCEPTABLE.
- ALTERNATE CONSTRUCTION ALLOWS FOR CABLE CONDUCTORS IN THE WIRING DIAGRAM USING THE FOLLOWING COLORS:
 LIGHT BLUE FOR WHT/BLU
 WHITE FOR WHT/ORG
 LIGHT GREEN FOR WHT/GRN
 LIGHT BROWN FOR WHT/BRN



WIRING DIAGRAM
568A

△6

0.15	0.5	203.2 (8.00)	9-219245-8
24.38	80	24536.4 (966.00)	8-219245-0
21.34	70	21488.4 (846.00)	7-219245-0
15.24	50	15392.4 (606.00)	5-219245-0
12.20	40	12344.4 (486.00)	4-219245-0
9.15	30	9296.4 (366.00)	3-219245-0
7.62	25	7721.6 (304.00)	2-219245-5
6.10	20	6197.6 (244.00)	2-219245-0
4.88	16	4978.4 (196.00)	1-219245-6
4.57	15	4724.4 (184.00)	1-219245-5
4.27	14	4368.8 (172.00)	1-219245-4
3.66	12	3759.2 (148.00)	1-219245-2
3.05	10	3149.6 (124.00)	1-219245-0
2.74	9	2794 (110.00)	219245-9
2.44	8	2489.2 (98.00)	219245-8
2.14	7	2184.4 (86.00)	219245-7
1.83	6	1879.6 (74.00)	219245-6
1.53	5	1574.8 (62.00)	219245-5
1.22	4	1270 (50.00)	219245-4
0.92	3	965.2 (38.00)	219245-3
0.61	2	660.4 (26.00)	219245-2
0.30	1	355.6 (14.00)	219245-1
METERS, REF	FEET, REF	DIM A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BOLES 25JUL97	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK B. ANTHONY 25JUL97	NAME B. ANTHONY	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - △2 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD B. ANTHONY 25JUL97	PRODUCT SPEC 108-1163	
MATERIAL - △3		FINISH -	APPLICATION SPEC 114-6053	RESTRICTED TO
		WEIGHT -	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=219245	SCALE NTS
			SHEET 1 of 1	REV G