


NUMBER
305183



1-305183-3	A.R.Z. POWER CONN.	.227	.243	4 ¹ / ₁₆
1-305183-2	M-N-LCK SOCKET	.111	.160	3 ¹⁵ / ₁₆
1-305183-1	M-N-LCK PIN	.087	.119	3 ¹⁵ / ₁₆
1-305183-0	NASA PATCH TIP	.113	.154	3 ¹⁵ / ₁₆
305183-7	8	.256	.284	4 ¹ / ₈
305183-6	10	.227	.251	4 ¹ / ₁₆
305183-5	12	.189	.206	4
305183-4	14	.162	.179	4
305183-3	16-20	.137	.155	3 ¹⁵ / ₁₆
305183-2	20	.103	.119	3 ¹⁵ / ₁₆
305183	16-20	.115	.129	3 ¹⁵ / ₁₆
PART NO.	SIZE	A	E	C

CUSTOMER COPY
REFERENCE ONLY

MATERIAL AND FINISH
STEEL & ALUMINUM
BLACK OXIDE



TE Connectivity

CLASS — # —

TYPE — # —

WIRE — RANGE — INSULATION — # —

TOLERANCE EXCEPT AS NOTED
± .015

SCALE — # —

LOC M

NO A

305183

REV G2

G2

REVISED PER ECO-11-005294

RK

HMR

05APR 11

LTR

REVISION RECORD

DR

CHK

DATE

DR

6/15/64

DE

APP

NAME

TOOL — EXTRACTION

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

36