










LOC	DIST	REVISIONS							
HM	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			G1	REVISED PER ECO-11--005033			21MAR11	RK	HMR
			G2	ADD 1/3, REV ECO-11-011931			10JUN2011	LH	SA



-  MATERIAL: HOUSING — POLYCARBONATE, 94V-0 RATED. SEE TABLE FOR COLOR.
110 BLOCKS — POLYCARBONATE, 94V-0 RATED.
JACK CONTACTS — PHOSPHOROUS BRONZE, PLATED WITH 1.27 μ m [.000050] MINIMUM THICK GOLD IN LOCALIZED AREA AND 3.81 μ m [.000150] MINIMUM THICK MATTE TIN IN SOLDER AREA OVER 1.27 μ m [.000050] MINIMUM THICK NICKEL UNDERPLATE.
2. 110 BLOCK WILL TERMINATE 22–26 AWG SOLID OR 7 STRAND CONDUCTORS, 1.27 [.050] MAXIMUM INSULATION DIAMETER.
3. MOUNTING PANEL THICKNESS 1.473 — 1.600 [.058 — .063].
-  ONE MODULAR JACK ASSEMBLY PER POLYBAG.
-  CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68 SUBPART F REQUIREMENTS.
-  THESE TWO SUGGESTED CUTOUT OPENINGS ARE USED IN TANDEM WITH DUAL FRONT AND BACK CUTOUTS.
-  TWENTY FIVE MODULAR JACK ASSEMBLIES PER POLYBAG.

	ALPINE WHITE	3-406372-3
	ELECTRIC IVORY	3-406372-1
	VIOLET	3-406372-0
	GREEN	2-406372-9
	YELLOW	2-406372-8
	RED	2-406372-7
	BLUE	2-406372-6
	ORANGE	2-406372-5
	NEMA GRAY	2-406372-4
	WHITE	2-406372-3
	BLACK	2-406372-2
	LIGHT ALMOND	2-406372-1
	ALPINE WHITE	1-406372-3
	ELECTRIC IVORY	1-406372-1
	VIOLET	1-406372-0
	GREEN	406372-9
	YELLOW	406372-8
	RED	406372-7
	BLUE	406372-6
	ORANGE	406372-5
PACKAGED	NEMA GRAY	406372-4
	WHITE	406372-3
	BLACK	406372-2
	LIGHT ALMOND	406372-1
	HOUSING COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25 NOV 96 DL DRUMMOND CHK 09 JAN 97 T. WOOTEN APVD 09 JAN 97 G. BOWMAN		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 110 MODULAR JACK ASSEMBLY, RJ45, ENHANCED CAT5, UNIVERSAL -	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [01] 3 PLC ± 0.13 [005] 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC 108-1389 APPLICATION SPEC 408-3389 WEIGHT -	
MATERIAL 				SIZE A1	
				CAGE CODE 00779	
				DRAWING NO C-406372	
				RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV G2	