




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		T2	REVISED PER ECO-11-004587	11MAR11	RK HMR



- 1
- FITS 0.81±0.025 X 6.35 [.032±.001 X .250] TAB
- 2
- WIRE SIZE: 1.3–2.0mm² [16–14 AWG], STRANDED ONLY.
STRIP LENGTH 7.94 [.312]
- 3
- INSULATION SIZE: 4.70 [.185] MAX DIA.
- 4
- CONTINUOUS STRIP.



BULK		TYPE 6/6 NYLON		BLUE TRANSLUCENT		0.41 [.016] #4H BRASS		TIN		5-520132-2			
STANDARD				BLACK TRANSLUCENT						9-520132-2			
PACKAGING		MATERIAL		COLOR		MATERIAL		FINISH		3-520132-2			
		HOUSING				TERMINAL				PART NO			
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN P FORTNEY CHK JR RUTH APVD DJ BRATINA 11/10/89 11/10/89 11/10/89		TE Connectivity							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-2043 APPLICATION SPEC 114-2123		NAME RECEPTACLE ASSEMBLY,ULTRA-FAST FLAG, 6.35 [.250] SERIES							
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.38 [.015] 4 PLC ± - ANGLES ± -		WEIGHT -		SIZE A2		CAGE CODE 00779		DRAWING NO C=520132		RESTRICTED TO -	
MATERIAL SEE TABLE		FINISH SEE TABLE		CUSTOMER DRAWING				SCALE 8:1		SHEET 1 of 1		REV T2	

