

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC

	DIST
--	------

REVISIONS

AF

50

	F
--	---

LTR

DESCRIPTION

DATE _____

DWN

	APVD
--	------

| K


REVISÉD PER ECR-12-005303

23JUL12

KH

KR

- 1 MATES WITH $.032 \pm .001 \times .250$ TAB
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .090—.160 DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA



HOUSING: NYLON, COLOR—BLUE TRANSLUCENT
RECEPTACLE: #3 HARD BRASS
TIN

3-520406-2

MATERIAL & FINISH

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	10/27/88
P FORTNEY	

CHK	11/3/88
-----	---------

MS FEHER

APVD
K RANDOLPH

PRODUCT SPEC	
--------------	--

108-204

APPLICATION SPEC

114-2123

WEIGHT	—
--------	---



TE Connectivity

8	NAME	RECEPTACLE ASSY,ULTRA-FAST PLUS, .250 SERIES,16-14 AWG
---	------	---

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A.3 00779 ©-520406

SCALE	4.1	SHEET	1 OF 1	REV	K
-------	-----	-------	--------	-----	---