


LOC	DIST	REVISIONS				
CE	16	P	LTR	DESCRIPTION	DATE	DWN
			A	RELEASE PER NPR	25 OCT 05	JD

- 1 MAXIMUM CONNECTOR INSERTION LOSS IS 0.5 dB PLUS CABLE
ATTENUATION OF 1.5dB/km AT 1300nm (SEE TABLE)
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF
TYCO ELECTRONICS STANDARD 230-702



0.95	300.00±3.00 [11811.02±118.11]	9-5492249-9
0.65	100.00±1.00 [3937.01±39.37]	9-5492249-8
0.55	35.00±0.35 [1377.95±14.00]	3-5492249-5
0.55	30.00±0.30 [1181.10±11.81]	3-5492249-0
0.54	25.00±0.30 [984.25±11.81]	2-5492249-5
0.53	20.00±0.30 [787.40±11.81]	2-5492249-0
0.52	15.00±0.15 [590.60±6.00]	1-5492249-5
0.52	10.00±0.15 [393.70±5.91]	1-5492249-0
0.51	8.00±0.15 [315.00±6.00]	5492249-8
0.51	6.00±0.08 [236.20±3.00]	5492249-6
0.51	5.00±0.08 [196.85±3.15]	5492249-5
0.50	3.00±0.05 [118.11±1.97]	5492249-3
0.50	2.00±0.05 [78.74±1.97]	5492249-2
0.50	1.00±0.05 [39.37±1.97]	5492249-1
MAX IL (dB)	1	L
		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
METERS [INCHES]

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN
C.S.VASU
25 OCT 05

CHK
J.DUNCAN
25 OCT 05

APVD
J.DUNCAN
25 OCT 05

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
CABLE ASSEMBLY, 62.5/125 LDD,
AMP SC DUPLEX (NG), OPTIMATE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=5492249

RESTRICTED TO
-

SCALE
NTS

SHEET
1

OF
1

REV
A