




- ⚠

MATERIAL: POLYPHENYLENE OXIDE MOLDING COMPOUND. SEE TABLE FOR COLOR.
2. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. 100 KITS BULK PACKAGED.



12.19-13.97[.480-.550]	ALMOND	4-552007-2	4-552006-2	4-552008-2
12.19-13.97[.480-.550]	BLACK	4-552007-1	4-552006-1	4-552008-1
8.38-9.65[.330-.380]	BLACK	3-552007-1	3-552006-1	3-552008-1
9.65-10.92[.380-.430]	BLACK	2-552007-1	2-552006-1	2-552008-1
10.92-12.45[.430-.490]	GRAY	552007-4	552006-4	552008-4
10.92-12.45[.430-.490]	BLACK	552007-1	552006-1	552008-1
CABLE RANGE DIAMETER	COLOR	GROOVE SIDE PART NO.	TONGUE SIDE PART NO.	KIT PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. STRAUSSER 16APR97	 TE Connectivity						
		CHK M. HUGHES 21APR97							
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. HUGHES 21APR97		NAME COVER KIT, 180 DEGREE, 50 POSITION, CHAMP				
	0 PLC ± -		PRODUCT SPEC						
	1 PLC ± -		—						
	2 PLC ± -		APPLICATION SPEC						
	3 PLC ± -		—						
	4 PLC ± -		—		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
	ANGLES ± -		WEIGHT		A2	00779	C=552008	—	
	FINISH		—						
	MATERIAL 	—		CUSTOMER DRAWING		SCALE		SHEET	

2:1	1 of 1	U1
-----	--------	----