





LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
HM	00				C	REV; EC 0B40-0204-02	17JUL02	66 SH

MATERIAL: PANEL-BLACK ANODIZED ALUMINUM WITH WHITE MARKINGS.
PRINTED CIRCUIT BOARD-LAMINATED PLASTIC SHEET,.062 [1.57] THICK.

2. 24 PORT CAPACITY,2 25-PAIR CABLE PER PANEL,4 WIRES PER PORT.


3. FOUR BLACK 12-24 X .50 LONG CARBON STEEL CROSS RECESSED PAN HEAD SCREWS AND FOUR BLACK 10-32 X .50 LONG CARBON STEEL RECESSED SCREWS FOR MOUNTING OF PANEL ARE SHIPPED LOOSE. NOT SHOWN ON DRAWING.

4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS.



TYPICAL SCHEMATIC FOR

CHAMP PLUG
MODULAR JACK
P2 TO 13 THRU 24



556183-1					
PART NO.					
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL			DR M.D.BYERLY 8-28-90 CHK APPD		
FINISH			AMP Incorporated Harrisburg, PA 17105-3608		
APPLICATION SPEC			NAME		
WEIGHT			PATCH PANEL ASSY, 24 PORT,6 POSITION/2 PAIR		
SIZE	CAGE CODE	DRAWING NO			
D	00779	556183			
SCALE	1:1	SHEET	1 OF 1		