


| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
| GP  | 00   |           |     |                           |         |     |      |
|     |      |           | P   | REVISED PER ECO-11-004835 | 11MAR11 | RK  | HMR  |

D

OPENING FOR CABLE  
(SEE DASH NO. FOR DIA.)



C


SIZE IDENTIFICATION LETTER  
MOLDED IN APPROXIMATE AREA  
SHOWN, SEE TABLE

#4-40 HEX NUT  
(QTY. 2)  
MATL: CARBON STEEL  
FINISH:

#4-40 FIL HD SCREW  
(QTY. 2)  
MATL: STEEL  
FINISH:

1.920  
±.015


AMP LOGO



TEXTURED  
FINISH

B

- PARTS PACKAGED UNASSEMBLED, AS A UNIT KIT.
- ZINC PLATED .000200-.000400 THICK, CLEAR CHROMATE COATING.



D


C

5745173

B

|                       |                     |                |
|-----------------------|---------------------|----------------|
| D                     | .280                | 5745173-5      |
| G                     | .350                | 5745173-4      |
| K                     | .430                | 5745173-3      |
| M                     | .480                | 5745173-2      |
| P                     | .530                | 5745173-1      |
| NECK<br>SIZE<br>IDENT | MAX<br>CABLE<br>DIA | PART<br>NUMBER |

A

|                                                                                       |                                        |                                |                                                                                                       |            |               |              |       |
|---------------------------------------------------------------------------------------|----------------------------------------|--------------------------------|-------------------------------------------------------------------------------------------------------|------------|---------------|--------------|-------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                        | DWN<br>B. MCMASTER<br>12AUG05  |  TE Connectivity |            |               |              |       |
|                                                                                       |                                        | CHK<br>C. ROHDE<br>12AUG05     |                                                                                                       |            |               |              |       |
| DIMENSIONS:<br>INCHES                                                                 |                                        | APVD<br>M. WALMSLEY<br>12AUG05 | NAME                                                                                                  |            |               |              |       |
|  | TOLERANCES UNLESS OTHERWISE SPECIFIED: | PRODUCT SPEC                   | CABLE CLAMP KIT, SIZE 3,<br>180 DEGREE, AMPLIMITE                                                     |            |               |              |       |
|                                                                                       | 0 PLC ± -                              | —                              |                                                                                                       |            |               |              |       |
|                                                                                       | 1 PLC ± -                              | —                              |                                                                                                       |            |               |              |       |
|                                                                                       | 2 PLC ± -                              | —                              |                                                                                                       |            |               |              |       |
|                                                                                       | 3 PLC ± -.005                          | —                              |                                                                                                       |            |               |              |       |
| 4 PLC ± .005                                                                          | —                                      |                                |                                                                                                       |            |               |              |       |
| ANGLES ± -                                                                            | APPLICATION SPEC                       | SIZE                           | CAGE CODE                                                                                             | DRAWING NO | RESTRICTED TO |              |       |
| MATERIAL                                                                              | FINISH                                 | WEIGHT —                       | A2                                                                                                    | 00779      | C-5745173     | —            |       |
| SEE CALLOUTS                                                                          | SEE CALLOUTS                           | CUSTOMER DRAWING               |                                                                                                       |            | SCALE 1:1     | SHEET 1 of 1 | REV P |