

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

© COPYRIGHT - R3



ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		S	REVISED PER ECR-11-018063	26DEC11	KH	PD


- 1 CONTINUOUS STRIP ON REELS
- 2 MATING TAB THK IS .032±.001.
- 3 WIRE SIZE IS #18-#14 AWG
- 4 INSULATION RANGE IS .120-.170 DIA.




SECTION B-B



SECTION C-C



SECTION D-D



— OBSOLETE	SILVER PLATE	61944-4
— OBSOLETE	PRE TIN PLATE	61944-3
	TIN	61944-2
	—	61944-1
	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 26JUL2002		 TE Connectivity				
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		CHK P DESANTIS 26JUL02		NAME		
	0 PLC ± -		APVD P DESANTIS 26JUL02		RECEPTACLE, FASTON, PIGGYBACK, 250 SERIES —			
	1 PLC ± -		PRODUCT SPEC					
	2 PLC ± -		—					
	3 PLC ± -.015		APPLICATION SPEC					
4 PLC ± -		114-2082		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL	FINISH	WEIGHT		A2	00779	C=61944	—	
H04 BRASS		SEE TABLE		CUSTOMER DRAWING				SCALE 6:1
						SHEET 1 of 1	REV S	